

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279660

Luminaire Tested: **LDA2B158027D010 EU2B15FL408027 2LBALD1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279660
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B158027D010 EU2B15FL408027 2LBALD1MW
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl w/lens Self-Flanged, MW
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1522.7 lumens
Efficiency: N/A
Efficacy: 108.0 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279660

CATALOG NUMBER: LDA2B158027D010 EU2B15FL408027 2LBALD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P279660

CATALOG NUMBER: LDA2B158027D010 EU2B15FL408027 2LBALD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96		
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92		
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89		
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85		
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82		
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79		
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77		
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74		
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72		
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2093778
5°	2049478
10°	1867977
15°	1459258
20°	863928
25°	321175
30°	100379
35°	44629
40°	20738
45°	9768
50°	5373
55°	3011
60°	1381
65°	817
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P279660

CATALOG NUMBER: LDA2B158027D010 EU2B15FL408027 2LBALD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	382.5	25.1
10°-20°	760.7	50.0
20°-30°	311.6	20.5
30°-40°	51.6	3.4
40°-50°	12.2	0.8
50°-60°	3.2	0.2
60°-70°	0.8	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1454.8	95.5
0°-40°	1506.4	98.9
0°-60°	1521.8	99.9
0°-90°	1522.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1522.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4244	
5°	4138	383
15°	2857	761
25°	590	312
35°	74	52
45°	14	12
55°	4	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279660

CATALOG NUMBER: LDA2B158027D010 EU2B15FL408027 2LBALD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4243.9
1°	4229.2
2°	4209.6
3°	4192.2
4°	4169.1
5°	4138.3
6°	4092.9
7°	4033.5
8°	3948.9
9°	3846.1
10°	3728.7
11°	3592.4
12°	3438.6
13°	3263.1
14°	3068.1
15°	2857.0
17.5°	2265.6
20°	1645.5
22.5°	1053.5
25°	590.0
27.5°	311.1
30°	176.2
32.5°	111.8
35°	74.1
37.5°	48.9
40°	32.2
42.5°	21.0
45°	14.0
47.5°	9.8
50°	7.0
52.5°	4.9
55°	3.5
57.5°	2.1
60°	1.4
62.5°	0.7
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279660

CATALOG NUMBER: LDA2B158027D010 EU2B15FL408027 2LBALD1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)