

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279663

Luminaire Tested: **LDA2B158027D010 EU2B15FL408027 2LBALD1WH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P279663  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B158027D010 EU2B15FL408027 2LBALD1WH  
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in  
ADJ spun Refl w/lens Self-Flanged, WH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1509.6 lumens  
Efficiency: N/A  
Efficacy: 107.1 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P279663

CATALOG NUMBER: LDA2B158027D010 EU2B15FL408027 2LBALD1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P279663

CATALOG NUMBER: LDA2B158027D010 EU2B15FL408027 2LBALD1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2075672
5°	2031798
10°	1851846
15°	1446642
20°	856473
25°	318399
30°	99467
35°	44268
40°	20545
45°	9698
50°	5296
55°	3011
60°	1381
65°	817
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P279663

CATALOG NUMBER: LDA2B158027D010 EU2B15FL408027 2LBALD1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	379.2	25.1
10°-20°	754.1	50.0
20°-30°	308.9	20.5
30°-40°	51.1	3.4
40°-50°	12.1	0.8
50°-60°	3.2	0.2
60°-70°	0.8	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1442.2	95.5
0°-40°	1493.4	98.9
0°-60°	1508.7	99.9
0°-90°	1509.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1509.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4207	
5°	4103	379
15°	2832	754
25°	585	309
35°	74	51
45°	14	12
55°	4	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279663

CATALOG NUMBER: LDA2B158027D010 EU2B15FL408027 2LBALD1WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4207.2
1°	4192.7
2°	4173.2
3°	4155.9
4°	4133.1
5°	4102.6
6°	4057.5
7°	3998.6
8°	3914.8
9°	3812.9
10°	3696.5
11°	3561.3
12°	3408.9
13°	3234.9
14°	3041.6
15°	2832.3
17.5°	2246.0
20°	1631.3
22.5°	1044.4
25°	584.9
27.5°	308.4
30°	174.6
32.5°	110.9
35°	73.5
37.5°	48.5
40°	31.9
42.5°	20.8
45°	13.9
47.5°	9.7
50°	6.9
52.5°	4.9
55°	3.5
57.5°	2.1
60°	1.4
62.5°	0.7
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279663

CATALOG NUMBER: LDA2B158027D010 EU2B15FL408027 2LBALD1WH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)