

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278759

Luminaire Tested: **LDA2B158027D010 EU2B15NFL258027 2LBAD1WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P278759
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B158027D010 EU2B15NFL258027 2LBAD1WH
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in ADJ spun Refl, Self-Flanged, WH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1479.3 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P278759

CATALOG NUMBER: LDA2B158027D010 EU2B15NFL258027 2LBAD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P278759

CATALOG NUMBER: LDA2B158027D010 EU2B15NFL258027 2LBAD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									50									30									10									0									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100													100															
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97													97															
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94													94															
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91													91															
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89													89															
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86													86															
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84													84															
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82													82															
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80													80															
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78													78															
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76													76															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3786453
5°	3492032
10°	2353219
15°	1160204
20°	495571
25°	194828
30°	76680
35°	33607
40°	16165
45°	7814
50°	4298
55°	2408
60°	1381
65°	817
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P278759

CATALOG NUMBER: LDA2B158027D010 EU2B15NFL258027 2LBAD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	597.3	40.4
10°-20°	643.3	43.5
20°-30°	185.7	12.6
30°-40°	39.2	2.6
40°-50°	9.7	0.7
50°-60°	2.8	0.2
60°-70°	0.9	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1426.3	96.4
0°-40°	1465.5	99.1
0°-60°	1477.9	99.9
0°-90°	1479.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1479.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7675	
5°	7051	597
15°	2272	643
25°	358	186
35°	56	39
45°	11	10
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278759

CATALOG NUMBER: LDA2B158027D010 EU2B15NFL258027 2LBAD1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	7674.8
1°	7626.7
2°	7545.1
3°	7434.8
4°	7278.6
5°	7051.1
6°	6744.2
7°	6343.7
8°	5851.2
9°	5277.0
10°	4697.3
11°	4111.2
12°	3558.0
13°	3066.9
14°	2635.0
15°	2271.5
17.5°	1501.3
20°	943.9
22.5°	580.4
25°	357.9
27.5°	218.4
30°	134.6
32.5°	85.1
35°	55.8
37.5°	37.0
40°	25.1
42.5°	17.4
45°	11.2
47.5°	7.0
50°	5.6
52.5°	4.2
55°	2.8
57.5°	2.1
60°	1.4
62.5°	1.4
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.0
77.5°	0.7
80°	0.0
82.5°	0.0



TEST NUMBER: P278759

CATALOG NUMBER: LDA2B158027D010 EU2B15NFL258027 2LBAD1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)