

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278762

Luminaire Tested: **LDA2B158027D010 EU2B15NFL258027 2LBALD1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P278762
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B158027D010 EU2B15NFL258027 2LBALD1LI
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in ADJ spun Refl w/lens Self-Flanged, H
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1379.9 lumens
Efficiency: N/A
Efficacy: 97.9 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P278762

CATALOG NUMBER: LDA2B158027D010 EU2B15NFL258027 2LBALD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P278762

CATALOG NUMBER: LDA2B158027D010 EU2B15NFL258027 2LBALD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97	97	97	97
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94	94	94	94
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91	91	91	91
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89	89	89	89
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86	86	86	86
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84	84	84	84
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82	82	82	82
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80	80	80	80
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	78	78	78
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76	76	76	76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3531829
5°	3257186
10°	2194962
15°	1082210
20°	462232
25°	181709
30°	71552
35°	31379
40°	15070
45°	7256
50°	3991
55°	2236
60°	1283
65°	817
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P278762

CATALOG NUMBER: LDA2B158027D010 EU2B15NFL258027 2LBALD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	557.1	40.4
10°-20°	600.0	43.5
20°-30°	173.2	12.6
30°-40°	36.6	2.7
40°-50°	9.0	0.7
50°-60°	2.6	0.2
60°-70°	0.9	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1330.4	96.4
0°-40°	1366.9	99.1
0°-60°	1378.5	99.9
0°-90°	1379.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1379.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7159	
5°	6577	557
15°	2119	600
25°	334	173
35°	52	37
45°	10	9
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278762

CATALOG NUMBER: LDA2B158027D010 EU2B15NFL258027 2LBALD1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	7158.7
1°	7113.8
2°	7037.6
3°	6934.8
4°	6789.1
5°	6576.9
6°	6290.6
7°	5917.1
8°	5457.7
9°	4922.1
10°	4381.4
11°	3834.8
12°	3318.7
13°	2860.6
14°	2457.8
15°	2118.8
17.5°	1400.4
20°	880.4
22.5°	541.4
25°	333.8
27.5°	203.7
30°	125.6
32.5°	79.4
35°	52.1
37.5°	34.5
40°	23.4
42.5°	16.3
45°	10.4
47.5°	6.5
50°	5.2
52.5°	3.9
55°	2.6
57.5°	2.0
60°	1.3
62.5°	1.3
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.0
77.5°	0.7
80°	0.0
82.5°	0.0



TEST NUMBER: P278762

CATALOG NUMBER: LDA2B158027D010 EU2B15NFL258027 2LBALD1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)