

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280415

Luminaire Tested: **LDA2B109024D010 EU2B10WFL559024 2LBALD1WH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P280415  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B109024D010 EU2B10WFL559024 2LBALD1WH  
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND  
2in ADJ spun Refl w/lens Self-Flanged, WH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 821.8 lumens  
Efficiency: N/A  
Efficacy: 82.2 lumens/watt  
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P280415

CATALOG NUMBER: LDA2B109024D010 EU2B10WFL559024 2LBALD1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P280415

CATALOG NUMBER: LDA2B109024D010 EU2B10WFL559024 2LBALD1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	97	95																																			
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90																																				
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85																																				
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80																																				
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76																																				
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72																																				
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69																																				
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65																																				
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62																																				
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59																																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	701758
5°	687501
10°	639291
15°	558165
20°	462127
25°	353456
30°	193408
35°	71612
40°	24795
45°	11164
50°	5296
55°	2580
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P280415

CATALOG NUMBER: LDA2B109024D010 EU2B10WFL559024 2LBALD1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	129.0	15.7
10°-20°	302.0	36.8
20°-30°	285.5	34.7
30°-40°	87.9	10.7
40°-50°	13.9	1.7
50°-60°	2.9	0.4
60°-70°	0.4	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	716.5	87.2
0°-40°	804.4	97.9
0°-60°	821.3	99.9
0°-90°	821.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	821.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1422	
5°	1388	129
15°	1093	302
25°	649	286
35°	119	88
45°	16	14
55°	3	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280415

CATALOG NUMBER: LDA2B109024D010 EU2B10WFL559024 2LBALD1WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1422.4
1°	1417.1
2°	1410.6
3°	1405.3
4°	1398.4
5°	1388.2
6°	1374.8
7°	1356.9
8°	1332.9
9°	1305.1
10°	1276.1
11°	1244.1
12°	1210.2
13°	1173.2
14°	1134.8
15°	1092.8
17.5°	982.0
20°	880.2
22.5°	777.0
25°	649.3
27.5°	495.4
30°	339.5
32.5°	208.4
35°	118.9
37.5°	66.3
40°	38.5
42.5°	24.0
45°	16.0
47.5°	10.7
50°	6.9
52.5°	4.6
55°	3.0
57.5°	1.9
60°	0.8
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280415

CATALOG NUMBER: LDA2B109024D010 EU2B10WFL559024 2LBALD1WH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)