

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P495604

Luminaire Tested: **LDA2B109024R60D010 2LBD1WHH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P495604  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-53)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B109024R60D010 2LBD1WHH  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2400K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 748.2 lumens  
Efficiency: N/A  
Efficacy: 74.8 lumens/watt  
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.87  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P495604

CATALOG NUMBER: LDA2B109024R60D010 2LBD1WHH

### Luminous Intensity Polar Plot





TEST NUMBER: P495604

CATALOG NUMBER: LDA2B109024R60D010 2LBD1WHH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86		91	87	85		88	86	84	82
4	98	91	86	81	96	90	85	81	88	83	80		86	82	79		84	81	78	77
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	70		77	72	69		75	72	69	67
7	85	76	70	66	83	75	69	66	74	69	65		73	68	65		71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64	60	57	56
10	73	64	58	55	72	64	58	54	63	58	54		62	57	54		61	57	54	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	447874
5°	425219
10°	416258
15°	402892
20°	368357
25°	327054
30°	244680
35°	138104
40°	51974
45°	23304
50°	11360
55°	2322
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P495604

CATALOG NUMBER: LDA2B109024R60D010 2LBD1WHH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	81.3	10.9
10°-20°	219.1	29.3
20°-30°	267.7	35.8
30°-40°	146.0	19.5
40°-50°	29.2	3.9
50°-60°	4.2	0.6
60°-70°	0.5	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	568.1	75.9
0°-40°	714.1	95.4
0°-60°	747.5	99.9
0°-90°	748.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	748.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	908	
5°	859	81
15°	789	219
25°	601	268
35°	229	146
45°	33	29
55°	3	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P495604

CATALOG NUMBER: LDA2B109024R60D010 2LBD1WHH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	907.8
1°	903.7
2°	895.7
3°	885.1
4°	869.9
5°	858.6
6°	852.5
7°	845.3
8°	839.6
9°	837.0
10°	830.9
11°	824.1
12°	818.0
13°	810.8
14°	800.2
15°	788.8
16°	774.4
17°	754.3
18°	741.4
19°	720.6
20°	701.6
21°	684.2
22.5°	655.0
23°	642.9
24°	624.3
25°	600.8
26°	570.9
27°	539.4
28°	503.4
29°	469.3
30°	429.5
32.5°	329.4
35°	229.3
37.5°	143.7
40°	80.7
42.5°	50.4
45°	33.4
47.5°	22.7
50°	14.8
52.5°	7.6
55°	2.7
57.5°	1.1
60°	0.8
62.5°	0.8
65°	0.4



TEST NUMBER: P495604

CATALOG NUMBER: LDA2B109024R60D010 2LBD1WHH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)