

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P497237

Luminaire Tested: **LDA2B158027R30D010 2LBDC1MB**

Issue Date: 3/12/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P497237
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-14)
Test Lab: INNOVATION CENTER
Issue Date: 3/12/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B158027R30D010 2LBDC1MB
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 2700K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1316.2 lumens
Efficiency: N/A
Efficacy: 93.4 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.46
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P497237

CATALOG NUMBER: LDA2B158027R30D010 2LBDC1MB

Luminous Intensity Polar Plot





TEST NUMBER: P497237

CATALOG NUMBER: LDA2B158027R30D010 2LBDC1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20															
RC	80					70					50					30					10					0										
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0						
RCR																																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100									
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	96	95	93	92	90	89	87	85	82	80	77	75	73				
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	93	95	93	92	90	89	87	85	82	80	77	75	73						
3	108	103	100	97	106	102	99	96	99	97	94	97	95	93	95	93	92	90	95	93	92	90	89	87	85	82	80	77	75	73						
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	92	90	89	87	92	90	89	87	85	82	80	77	75	73								
5	101	95	91	88	100	95	91	88	93	90	87	91	89	86	90	88	86	85	90	88	86	85	83	82	80	77	75	73								
6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	88	85	83	82	88	85	83	82	80	77	75	73										
7	96	89	85	82	95	89	85	82	87	84	81	86	83	81	85	83	81	80	85	83	81	80	77	75	73											
8	93	86	82	79	92	86	82	79	85	81	79	84	81	79	83	81	78	77	83	81	78	77	75	73												
9	90	84	80	77	90	83	80	77	83	79	77	82	79	76	81	78	76	75	81	78	76	75	73													
10	88	81	77	75	87	81	77	75	80	77	75	80	77	74	79	76	74	73	79	76	74	73														

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2550779
5°	2432105
10°	1972380
15°	1205714
20°	526810
25°	197114
30°	81693
35°	38185
40°	17775
45°	8652
50°	4759
55°	1806
60°	691
65°	817
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P497237

CATALOG NUMBER: LDA2B158027R30D010 2LBDC1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	438.1	33.3
10°-20°	632.5	48.1
20°-30°	188.8	14.3
30°-40°	43.4	3.3
40°-50°	10.7	0.8
50°-60°	2.4	0.2
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1259.3	95.7
0°-40°	1302.7	99.0
0°-60°	1315.8	100.0
0°-90°	1316.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1316.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5170	
5°	4911	438
15°	2361	632
25°	362	189
35°	63	43
45°	12	11
55°	2	2
65°	1	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P497237

CATALOG NUMBER: LDA2B158027R30D010 2LBDC1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	5170.2
1°	5158.5
2°	5106.1
3°	5070.9
4°	5005.4
5°	4910.9
6°	4781.9
7°	4628.1
8°	4432.3
9°	4193.7
10°	3937.1
11°	3662.7
12°	3350.9
13°	3015.8
14°	2697.2
15°	2360.6
16°	2035.1
17°	1714.4
18°	1455.8
19°	1204.8
20°	1003.4
21°	813.1
22.5°	602.7
23°	543.4
24°	444.8
25°	362.1
26°	297.2
27°	247.6
28°	204.1
29°	171.0
30°	143.4
32.5°	93.8
35°	63.4
37.5°	42.1
40°	27.6
42.5°	17.9
45°	12.4
47.5°	9.0
50°	6.2
52.5°	4.1
55°	2.1
57.5°	1.4
60°	0.7
62.5°	0.7
65°	0.7



TEST NUMBER: P497237

CATALOG NUMBER: LDA2B158027R30D010 2LBDC1MB

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)