

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P495645

Luminaire Tested: **LDA2B109024R70D010 2LBD1LI**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P495645  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-79)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B109024R70D010 2LBD1LI  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2400K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 743.4 lumens  
Efficiency: N/A  
Efficacy: 74.3 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.09  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P495645  
CATALOG NUMBER: LDA2B109024R70D010 2LBD1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P495645

CATALOG NUMBER: LDA2B109024R70D010 2LBD1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85	82	80	78
4	95	87	81	77	93	86	81	76	84	79	75		82	78	74		80	76	74	72
5	90	81	75	70	88	80	74	70	78	73	69		76	72	68		75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70	66	62	61
7	80	70	63	59	79	69	63	59	68	62	58		67	62	58		66	61	58	56
8	76	65	59	54	74	65	59	54	64	58	54		62	57	54		61	57	54	52
9	71	61	55	50	70	61	54	50	60	54	50		59	54	50		58	53	50	48
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54	50	46	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	290442
5°	287243
10°	285805
15°	284803
20°	274640
25°	263309
30°	260631
35°	222604
40°	138919
45°	64260
50°	23256
55°	1634
60°	789
65°	934
70°	577
75°	762
80°	0
85°	0



TEST NUMBER: P495645

CATALOG NUMBER: LDA2B109024R70D010 2LBD1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.0	7.4
10°-20°	156.2	21.0
20°-30°	224.6	30.2
30°-40°	221.4	29.8
40°-50°	78.9	10.6
50°-60°	6.5	0.9
60°-70°	0.6	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	435.7	58.6
0°-40°	657.1	88.4
0°-60°	742.5	99.9
0°-90°	743.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	743.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	589	
5°	580	55
15°	558	156
25°	484	225
35°	370	221
45°	92	79
55°	2	6
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P495645

CATALOG NUMBER: LDA2B109024R70D010 2LBD1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	588.7
1°	588.7
2°	587.5
3°	587.9
4°	583.0
5°	580.0
6°	575.8
7°	574.3
8°	572.4
9°	572.0
10°	570.5
11°	568.6
12°	568.6
13°	565.2
14°	560.6
15°	557.6
16°	551.5
17°	548.1
18°	537.5
19°	530.3
20°	523.1
21°	513.6
22.5°	500.4
23°	495.1
24°	490.1
25°	483.7
26°	479.9
27°	473.4
28°	472.7
29°	465.9
30°	457.5
32.5°	425.3
35°	369.6
37.5°	297.2
40°	215.7
42.5°	147.5
45°	92.1
47.5°	55.0
50°	30.3
52.5°	11.4
55°	1.9
57.5°	1.1
60°	0.8
62.5°	0.8
65°	0.8



TEST NUMBER: P495645

CATALOG NUMBER: LDA2B109024R70D010 2LBD1LI

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)