

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P495661

Luminaire Tested: **LDA2B109024R70D010 2LBDL1WMH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P495661
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B109024R70D010 2LBDL1WMH
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2400K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 688.2 lumens
Efficiency: N/A
Efficacy: 68.8 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P495661

CATALOG NUMBER: LDA2B109024R70D010 2LBDL1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P495661

CATALOG NUMBER: LDA2B109024R70D010 2LBDL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93				93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85				85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78				78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72				72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	74	71	67	66				66
6	85	75	68	64	83	74	68	63	72	67	63	71	66	63	70	65	62	61				61
7	80	70	63	59	78	69	63	58	68	62	58	66	61	58	65	61	57	56				56
8	75	65	58	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52				52
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48				48
10	68	57	51	46	66	57	50	46	56	50	46	55	50	46	54	49	46	45				45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	272484
5°	270900
10°	269072
15°	264066
20°	254532
25°	243712
30°	232147
35°	191526
40°	124493
45°	65027
50°	30241
55°	11096
60°	1085
65°	934
70°	577
75°	762
80°	0
85°	0



TEST NUMBER: P495661

CATALOG NUMBER: LDA2B109024R70D010 2LBDL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.7	7.5
10°-20°	145.3	21.1
20°-30°	206.2	30.0
30°-40°	192.8	28.0
40°-50°	77.6	11.3
50°-60°	13.6	2.0
60°-70°	0.7	0.1
70°-80°	0.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	403.3	58.6
0°-40°	596.1	86.6
0°-60°	687.2	99.8
0°-90°	688.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	688.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	552	
5°	547	52
15°	517	145
25°	448	206
35°	318	193
45°	93	78
55°	13	14
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P495661

CATALOG NUMBER: LDA2B109024R70D010 2LBDL1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	552.3
1°	553.1
2°	551.9
3°	549.6
4°	548.5
5°	547.0
6°	540.9
7°	542.8
8°	537.5
9°	536.4
10°	537.1
11°	532.2
12°	531.1
13°	525.0
14°	522.7
15°	517.0
16°	513.6
17°	506.8
18°	498.8
19°	494.3
20°	484.8
21°	477.6
22.5°	464.3
23°	460.9
24°	454.5
25°	447.7
26°	442.4
27°	434.8
28°	427.2
29°	418.1
30°	407.5
32.5°	370.3
35°	318.0
37.5°	256.2
40°	193.3
42.5°	138.0
45°	93.2
47.5°	61.4
50°	39.4
52.5°	24.6
55°	12.9
57.5°	4.2
60°	1.1
62.5°	0.8
65°	0.8



TEST NUMBER: P495661

CATALOG NUMBER: LDA2B109024R70D010 2LBDL1WMH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)