

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P315657

Luminaire Tested: **LDA2B10WFL9024D010 PIN1MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P315657  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1809-951-61)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B10WFL9024D010 PIN1MW  
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND  
2in Adj PinHole, Black oculus, matte white finish  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 644.8 lumens  
Efficiency: N/A  
Efficacy: 64.5 lumens/watt  
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.68  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P315657

CATALOG NUMBER: LDA2B10WFL9024D010 PIN1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P315657

CATALOG NUMBER: LDA2B10WFL9024D010 PIN1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	101	98	107	103	99	96	100	97	94	97	94	92	94	92	90	89			
3	104	98	94	90	102	97	93	89	94	91	88	92	89	87	90	87	85	84			
4	100	93	88	84	98	92	87	83	90	86	82	88	84	81	86	83	81	79			
5	95	88	82	79	94	87	82	78	85	81	78	84	80	77	82	79	76	75			
6	91	83	78	74	90	82	77	74	81	77	73	80	76	73	78	75	72	71			
7	87	79	74	70	86	78	73	70	77	73	69	76	72	69	75	71	69	67			
8	84	75	70	66	83	75	70	66	74	69	66	73	69	66	72	68	65	64			
9	81	72	67	63	80	71	66	63	71	66	63	70	66	63	69	65	62	61			
10	77	69	64	60	76	68	63	60	68	63	60	67	63	60	66	62	60	58			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	586508	586508	586508
5°	568889	570276	567701
10°	520761	518657	515551
15°	438033	442068	437318
20°	334966	343839	334388
25°	212683	239793	216875
30°	123736	139687	125900
35°	65408	69564	65589
40°	34520	36066	34520
45°	19327	20025	19536
50°	9057	11436	9057
55°	3269	6279	3527
60°	3750	3750	3750
65°	4086	4436	4086
70°	5049	4472	5049
75°	4575	4575	4575
80°	4830	3978	4830
85°	3962	3962	3962



TEST NUMBER: P315657

CATALOG NUMBER: LDA2B10WFL9024D010 PIN1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	106.1	16.5
10°-20°	236.3	36.6
20°-30°	190.8	29.6
30°-40°	75.4	11.7
40°-50°	23.2	3.6
50°-60°	6.0	0.9
60°-70°	3.6	0.6
70°-80°	2.6	0.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	533.2	82.7
0°-40°	608.6	94.4
0°-60°	637.8	98.9
0°-90°	644.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	644.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1189	1189	1189	1189	1189	
5°	1149	1151	1152	1149	1146	106
15°	858	860	866	862	856	236
25°	391	409	440	417	398	182
35°	109	112	116	112	109	73
45°	28	28	29	28	28	23
55°	4	5	7	5	4	5
65°	4	4	4	4	4	4
75°	2	2	2	2	2	3
85°	1	1	1	1	1	1
90°	0	0	0	0	0	



TEST NUMBER: P315657

CATALOG NUMBER: LDA2B10WFL9024D010 PIN1MW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1188.8	1188.8	1188.8	1188.8	1188.8
2.5°	1174.0	1174.7	1175.7	1174.3	1170.9
5°	1148.7	1150.8	1151.5	1149.1	1146.3
7.5°	1107.2	1104.8	1106.9	1102.7	1099.3
10°	1039.5	1036.3	1035.3	1029.1	1029.1
12.5°	955.8	954.7	955.4	952.3	947.5
15°	857.6	860.0	865.5	862.1	856.2
17.5°	753.5	756.9	761.8	760.7	752.8
20°	638.0	648.0	654.9	648.4	636.9
22.5°	506.6	528.0	545.7	531.8	513.2
25°	390.7	409.4	440.5	417.0	398.4
27.5°	296.3	309.8	338.2	315.0	302.2
30°	217.2	225.5	245.2	230.0	221.0
32.5°	155.3	161.1	169.4	160.4	156.0
35°	108.6	111.7	115.5	112.0	108.9
37.5°	76.4	77.5	80.2	77.5	76.1
40°	53.6	53.9	56.0	54.3	53.6
42.5°	38.7	38.7	39.8	39.1	38.7
45°	27.7	28.0	28.7	28.4	28.0
47.5°	19.7	20.4	20.4	20.7	19.4
50°	11.8	14.5	14.9	14.5	11.8
52.5°	6.2	8.6	10.7	8.6	6.2
55°	3.8	5.2	7.3	5.2	4.1
57.5°	3.8	3.8	4.8	4.1	3.8
60°	3.8	3.8	3.8	3.8	3.8
62.5°	3.8	3.8	3.8	3.8	3.8
65°	3.5	3.8	3.8	3.8	3.5
67.5°	3.5	3.5	3.5	3.5	3.5
70°	3.5	3.5	3.1	3.5	3.5
72.5°	3.1	3.1	2.8	3.1	3.1
75°	2.4	2.4	2.4	2.4	2.4
77.5°	2.1	2.1	2.1	2.1	2.1
80°	1.7	1.7	1.4	1.7	1.7
82.5°	1.0	1.0	1.0	1.0	1.0
85°	0.7	0.7	0.7	0.7	0.7
87.5°	0.3	0.3	0.3	0.3	0.3
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°    - - 45°-225°    - - - - 90°-270°







(END OF REPORT)