

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P495704

Luminaire Tested: **LDA2B109027R20D010 2LBDLC1MMS-30DEG TILT**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P495704
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B109027R20D010 2LBDLC1MMS-30DEG TILT
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2700K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 532.7 lumens
Efficiency: N/A
Efficacy: 53.3 lumens/watt
Spacing Criteria (0/90/45): 2.56 / 0.56 / 1.2
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P495704

CATALOG NUMBER: LDA2B109027R20D010 2LBDLC1MMS-30DEG TILT

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P495704

CATALOG NUMBER: LDA2B109027R20D010 2LBDLC1MMS-30DEG TILT

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91					91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82					82			
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74					74			
4	92	83	76	71	90	82	75	70	79	74	70	77	73	69	75	71	68	66					66			
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59					59			
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53					53			
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48					48			
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43					43			
9	64	53	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38					38			
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34					34			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	8486	8486	8486
5°	16195	7478	5448
10°	38675	6563	3707
15°	225299	5210	1481
20°	1123868	3203	420
25°	2049260	1089	0
30°	2403558	0	0
35°	2103716	0	0
40°	1553549	0	0
45°	559989	0	0
50°	116589	0	0
55°	26665	344	0
60°	8486	395	0
65°	1868	934	0
70°	0	1154	577
75°	0	1525	0
80°	0	2273	0
85°	0	4529	0



TEST NUMBER: P495704

CATALOG NUMBER: LDA2B109027R20D010 2LBDLC1MMS-30DEG TILT

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1.9	0.4
10°-20°	29.3	5.5
20°-30°	197.3	37.0
30°-40°	230.5	43.3
40°-50°	67.2	12.6
50°-60°	4.5	0.8
60°-70°	0.8	0.2
70°-80°	0.7	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	228.5	42.9
0°-40°	459.0	86.2
0°-60°	530.7	99.6
0°-90°	532.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	532.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	17	17	17	17	17	
5°	33	24	15	13	11	4
15°	441	50	10	5	3	230
25°	3764	77	2	0	0	1667
35°	3493	42	0	0	0	2146
45°	803	9	0	0	0	740
55°	31	2	0	0	0	39
65°	2	1	1	1	0	3
75°	0	1	1	1	0	0
85°	0	1	1	1	0	0
90°	0	0	0	0	0	



TEST NUMBER: P495704

CATALOG NUMBER: LDA2B109027R20D010 2LBDLC1MMS-30DEG TILT

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	17.2	17.2	17.2	17.2	17.2	17.2	17.2	17.2	17.2
2.5°	22.1	22.1	19.6	17.6	15.9	15.1	14.7	13.9	13.5
5°	32.7	28.6	23.7	18.4	15.1	13.9	12.7	11.4	11.0
7.5°	47.8	41.7	28.6	18.8	14.3	12.3	11.0	9.8	9.0
10°	77.2	60.0	35.1	18.8	13.1	10.6	9.0	7.8	7.4
12.5°	142.5	91.9	42.1	18.4	11.8	9.0	6.9	6.1	4.9
15°	441.1	190.3	49.8	17.6	10.2	6.9	5.3	3.3	2.9
17.5°	1140.8	444.4	55.5	15.5	8.2	4.9	2.5	2.0	2.0
20°	2140.6	805.8	63.7	13.5	6.1	3.3	1.6	1.2	0.8
21°	2442.0	986.0	67.8	12.7	5.3	2.0	1.2	0.4	0.4
22°	2910.5	1182.4	71.1	11.8	4.5	1.2	0.8	0.4	0.0
23°	3244.2	1307.8	74.3	10.6	3.3	1.2	0.4	0.0	0.0
24°	3577.9	1467.5	76.4	9.8	2.9	0.8	0.4	0.0	0.0
25°	3764.5	1600.7	77.2	9.0	2.0	0.4	0.0	0.0	0.0
26°	3918.1	1689.7	77.6	8.2	1.2	0.0	0.0	0.0	0.0
27°	4049.6	1793.0	76.8	7.4	1.2	0.0	0.0	0.0	0.0
28°	4124.4	1810.2	75.6	6.5	0.4	0.0	0.0	0.0	0.0
29°	4156.6	1789.4	71.9	5.7	0.4	0.0	0.0	0.0	0.0
30°	4219.1	1769.7	68.2	5.3	0.0	0.0	0.0	0.0	0.0
31°	4161.5	1704.8	63.7	4.5	0.0	0.0	0.0	0.0	0.0
32°	3936.1	1650.1	58.4	3.7	0.0	0.0	0.0	0.0	0.0
33°	3868.7	1537.8	52.7	3.3	0.0	0.0	0.0	0.0	0.0
34°	3741.7	1370.7	47.8	2.9	0.0	0.0	0.0	0.0	0.0
35°	3492.9	1232.7	41.7	2.5	0.0	0.0	0.0	0.0	0.0
36°	3319.3	1075.0	36.4	2.0	0.0	0.0	0.0	0.0	0.0
37°	3137.6	937.4	32.3	1.6	0.0	0.0	0.0	0.0	0.0
38°	2911.7	792.8	27.4	1.2	0.0	0.0	0.0	0.0	0.0
39°	2648.7	655.1	23.3	1.2	0.0	0.0	0.0	0.0	0.0
40°	2412.2	528.1	20.0	0.8	0.0	0.0	0.0	0.0	0.0
42.5°	1488.7	301.4	11.8	0.8	0.0	0.0	0.0	0.0	0.0
45°	802.6	183.0	8.6	0.4	0.0	0.0	0.0	0.0	0.0
47.5°	369.6	85.4	6.1	0.4	0.0	0.0	0.0	0.0	0.0
50°	151.9	38.0	4.5	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	54.7	21.2	2.9	0.0	0.0	0.4	0.0	0.0	0.0
55°	31.0	12.3	1.6	0.4	0.4	0.4	0.4	0.0	0.0
57.5°	14.7	6.9	0.4	0.4	0.4	0.4	0.4	0.0	0.0
60°	8.6	3.7	0.4	0.4	0.4	0.8	0.4	0.0	0.0
62.5°	4.1	1.2	0.4	0.8	0.8	0.8	0.8	0.4	0.0
65°	1.6	0.4	0.8	0.8	0.8	1.2	0.8	0.4	0.0
67.5°	0.4	0.4	0.8	0.8	0.8	1.2	0.8	0.4	0.4
70°	0.0	0.4	0.8	0.8	0.8	1.2	0.8	0.4	0.4
72.5°	0.0	0.4	0.8	0.8	0.8	1.2	0.8	0.4	0.4
75°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.0
77.5°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.0
80°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.0



TEST NUMBER: P495704

CATALOG NUMBER: LDA2B109027R20D010 2LBDLC1MMS-30DEG TILT

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
82.5°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.0
85°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.0
87.5°	0.0	0.4	0.8	0.8	0.8	0.8	0.4	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)