

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P495743

Luminaire Tested: **LDA2B109027R30D010 2LBDLC1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P495743
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-16)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B109027R30D010 2LBDLC1MMS
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2700K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 779.5 lumens
Efficiency: N/A
Efficacy: 78.0 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.46
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P495743

CATALOG NUMBER: LDA2B109027R30D010 2LBDLC1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P495743

CATALOG NUMBER: LDA2B109027R30D010 2LBDLC1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10							
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10				
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	111	106	106	106	106	102	102	102	102	100	100	100	100
1	115	113	111	109	113	111	109	108	107	106	104	104	103	102	101	101	100	99	98	98	97	97	97	97
2	111	108	105	102	109	106	103	101	103	101	99	99	100	98	97	97	97	96	95	95	93	93	93	93
3	108	103	100	97	106	102	99	96	99	97	94	94	97	95	93	93	95	93	92	92	90	90	90	90
4	104	99	95	92	103	98	94	92	96	93	91	91	94	92	90	90	92	90	89	89	87	87	87	87
5	101	95	91	88	100	95	91	88	93	90	87	87	91	89	86	86	90	88	86	86	85	85	85	85
6	98	92	88	85	97	91	88	85	90	87	84	84	89	86	84	84	88	85	83	83	82	82	82	82
7	96	89	85	82	95	89	85	82	87	84	81	81	86	83	81	81	85	83	81	81	80	80	80	80
8	93	86	82	79	92	86	82	79	85	81	79	79	84	81	79	79	83	81	78	78	77	77	77	77
9	90	84	80	77	90	83	80	77	83	79	77	77	82	79	76	76	81	78	76	76	75	75	75	75
10	88	81	77	75	87	81	77	75	80	77	75	75	80	77	74	74	79	76	74	74	73	73	73	73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1510674
5°	1440424
10°	1168168
15°	714102
20°	312022
25°	116712
30°	48423
35°	22646
40°	10498
45°	5163
50°	2840
55°	1032
60°	395
65°	467
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P495743

CATALOG NUMBER: LDA2B109027R30D010 2LBDLC1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	259.5	33.3
10°-20°	374.6	48.1
20°-30°	111.8	14.3
30°-40°	25.7	3.3
40°-50°	6.3	0.8
50°-60°	1.4	0.2
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	745.8	95.7
0°-40°	771.5	99.0
0°-60°	779.3	100.0
0°-90°	779.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	779.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3062	
5°	2908	259
15°	1398	375
25°	214	112
35°	38	26
45°	7	6
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P495743

CATALOG NUMBER: LDA2B109027R30D010 2LBDLC1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	3062.0
1°	3055.1
2°	3024.1
3°	3003.2
4°	2964.4
5°	2908.5
6°	2832.1
7°	2741.0
8°	2625.0
9°	2483.7
10°	2331.8
11°	2169.2
12°	1984.6
13°	1786.1
14°	1597.4
15°	1398.1
16°	1205.3
17°	1015.4
18°	862.2
19°	713.5
20°	594.3
21°	481.5
22.5°	357.0
23°	321.8
24°	263.4
25°	214.4
26°	176.0
27°	146.6
28°	120.9
29°	101.3
30°	85.0
32.5°	55.5
35°	37.6
37.5°	24.9
40°	16.3
42.5°	10.6
45°	7.4
47.5°	5.3
50°	3.7
52.5°	2.5
55°	1.2
57.5°	0.8
60°	0.4
62.5°	0.4
65°	0.4



TEST NUMBER: P495743

CATALOG NUMBER: LDA2B109027R30D010 2LBDLC1MMS

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)