

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279674

Luminaire Tested: **LDA2B158030D010 EU2B15FL408030 2LBALD1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279674
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B158030D010 EU2B15FL408030 2LBALD1LI
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl w/lens Self-Flanged, H
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1540.1 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279674

CATALOG NUMBER: LDA2B158030D010 EU2B15FL408030 2LBALD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P279674

CATALOG NUMBER: LDA2B158030D010 EU2B15FL408030 2LBALD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																											
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																											
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89																											
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85																											
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82																											
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79																											
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																											
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																											
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72																											
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2117755
5°	2072953
10°	1889368
15°	1475960
20°	873851
25°	324822
30°	101518
35°	45111
40°	20931
45°	9838
50°	5449
55°	3011
60°	1381
65°	817
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P279674

CATALOG NUMBER: LDA2B158030D010 EU2B15FL408030 2LBALD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	386.9	25.1
10°-20°	769.4	50.0
20°-30°	315.1	20.5
30°-40°	52.1	3.4
40°-50°	12.3	0.8
50°-60°	3.3	0.2
60°-70°	0.8	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1471.5	95.5
0°-40°	1523.6	98.9
0°-60°	1539.2	99.9
0°-90°	1540.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1540.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4292	
5°	4186	387
15°	2890	769
25°	597	315
35°	75	52
45°	14	12
55°	4	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279674

CATALOG NUMBER: LDA2B158030D010 EU2B15FL408030 2LBALD1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4292.5
1°	4277.6
2°	4257.8
3°	4240.2
4°	4216.8
5°	4185.7
6°	4139.8
7°	4079.7
8°	3994.1
9°	3890.2
10°	3771.4
11°	3633.5
12°	3478.0
13°	3300.5
14°	3103.2
15°	2889.7
17.5°	2291.5
20°	1664.4
22.5°	1065.5
25°	596.7
27.5°	314.6
30°	178.2
32.5°	113.1
35°	74.9
37.5°	49.5
40°	32.5
42.5°	21.2
45°	14.1
47.5°	9.9
50°	7.1
52.5°	4.9
55°	3.5
57.5°	2.1
60°	1.4
62.5°	0.7
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279674

CATALOG NUMBER: LDA2B158030D010 EU2B15FL408030 2LBALD1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)