

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278782

Luminaire Tested: **LDA2B158030D010 EU2B15NFL258030 2LBALD1WMH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P278782  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B158030D010 EU2B15NFL258030 2LBALD1WMH  
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC  
AND 2in ADJ spun Refl w/lens Self-Flanged, WMH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1406.5 lumens  
Efficiency: N/A  
Efficacy: 99.8 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P278782

CATALOG NUMBER: LDA2B158030D010 EU2B15NFL258030 2LBALD1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P278782

CATALOG NUMBER: LDA2B158030D010 EU2B15NFL258030 2LBALD1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97			97																
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94			94																
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91			91																
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89			89																
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86			86																
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84			84																
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82			82																
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80			80																
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78			78																
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76			76																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3599913
5°	3319983
10°	2237244
15°	1103050
20°	471157
25°	185247
30°	72920
35°	31981
40°	15393
45°	7396
50°	4068
55°	2322
60°	1283
65°	817
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P278782

CATALOG NUMBER: LDA2B158030D010 EU2B15NFL258030 2LBALD1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	567.9	40.4
10°-20°	611.6	43.5
20°-30°	176.6	12.6
30°-40°	37.3	2.7
40°-50°	9.2	0.7
50°-60°	2.7	0.2
60°-70°	0.9	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1356.0	96.4
0°-40°	1393.3	99.1
0°-60°	1405.1	99.9
0°-90°	1406.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1406.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7297	
5°	6704	568
15°	2160	612
25°	340	177
35°	53	37
45°	11	9
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278782

CATALOG NUMBER: LDA2B158030D010 EU2B15NFL258030 2LBALD1WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7296.7
1°	7250.9
2°	7173.3
3°	7068.5
4°	6920.0
5°	6703.7
6°	6411.9
7°	6031.2
8°	5562.9
9°	5017.0
10°	4465.8
11°	3908.7
12°	3382.7
13°	2915.8
14°	2505.2
15°	2159.6
17.5°	1427.4
20°	897.4
22.5°	551.8
25°	340.3
27.5°	207.6
30°	128.0
32.5°	80.9
35°	53.1
37.5°	35.2
40°	23.9
42.5°	16.6
45°	10.6
47.5°	6.6
50°	5.3
52.5°	4.0
55°	2.7
57.5°	2.0
60°	1.3
62.5°	1.3
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.0
77.5°	0.7
80°	0.0
82.5°	0.0



TEST NUMBER: P278782

CATALOG NUMBER: LDA2B158030D010 EU2B15NFL258030 2LBALD1WMH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)