

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P495855

Luminaire Tested: **LDA2B109027R65D010 2LBDLC1MB**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P495855  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-68)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B109027R65D010 2LBDLC1MB  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2700K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 827.0 lumens  
Efficiency: N/A  
Efficacy: 82.7 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.94  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P495855

CATALOG NUMBER: LDA2B109027R65D010 2LBDLC1MB

### Luminous Intensity Polar Plot





TEST NUMBER: P495855

CATALOG NUMBER: LDA2B109027R65D010 2LBDLC1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	87
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	78	76	74
5	92	83	77	73	90	82	76	72	80	75	72	79	74	71	77	73	70	69
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60
8	78	68	62	58	77	68	62	58	67	61	58	66	61	57	65	60	57	56
9	74	64	58	54	73	64	58	54	63	58	54	62	57	54	61	57	53	52
10	71	61	55	51	70	60	54	51	59	54	50	59	54	50	58	53	50	49

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	432678
5°	414670
10°	394867
15°	375311
20°	349089
25°	322264
30°	279658
35°	200621
40°	108971
45°	46538
50°	20033
55°	7225
60°	1283
65°	1051
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P495855

CATALOG NUMBER: LDA2B109027R65D010 2LBDLC1MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	78.4	9.5
10°-20°	205.8	24.9
20°-30°	269.1	32.5
30°-40°	204.7	24.8
40°-50°	59.2	7.2
50°-60°	8.9	1.1
60°-70°	0.8	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	553.3	66.9
0°-40°	758.0	91.7
0°-60°	826.1	99.9
0°-90°	827.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	827.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	877	
5°	837	78
15°	735	206
25°	592	269
35°	333	205
45°	67	59
55°	8	9
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P495855

CATALOG NUMBER: LDA2B109027R65D010 2LBDLC1MB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	877.0
1°	873.9
2°	869.1
3°	859.3
4°	848.7
5°	837.3
6°	826.2
7°	816.5
8°	807.2
9°	798.8
10°	788.2
11°	778.9
12°	769.2
13°	759.5
14°	748.9
15°	734.8
16°	724.1
17°	711.3
18°	691.9
19°	681.7
20°	664.9
21°	649.9
22.5°	626.9
23°	618.1
24°	604.4
25°	592.0
26°	575.7
27°	557.6
28°	537.7
29°	516.5
30°	490.9
32.5°	420.6
35°	333.1
37.5°	245.7
40°	169.2
42.5°	107.4
45°	66.7
47.5°	41.5
50°	26.1
52.5°	15.5
55°	8.4
57.5°	3.1
60°	1.3
62.5°	0.9
65°	0.9



TEST NUMBER: P495855

CATALOG NUMBER: LDA2B109027R65D010 2LBDLC1MB

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)