

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278095

Luminaire Tested: **LDA2B158030D010 EU2B15SP158030 2LBAD1WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P278095
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B158030D010 EU2B15SP158030 2LBAD1WH
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH SPOT OPTIC AND 2in
ADJ spun Refl, Self-Flanged, WH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1439.6 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P278095

CATALOG NUMBER: LDA2B158030D010 EU2B15SP158030 2LBAD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P278095

CATALOG NUMBER: LDA2B158030D010 EU2B15SP158030 2LBAD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1 | 116 | 114 | 112 | 110 | 113 | 112 | 110 | 109 | 108 | 106 | 105 | 104 | 103 | 102 | 101 | 100 | 99 | 98 |
| 2 | 112 | 109 | 107 | 104 | 110 | 108 | 105 | 103 | 105 | 103 | 101 | 102 | 100 | 99 | 99 | 98 | 97 | 96 |
| 3 | 109 | 105 | 102 | 100 | 108 | 104 | 101 | 99 | 102 | 99 | 98 | 100 | 98 | 96 | 97 | 96 | 95 | 93 |
| 4 | 107 | 102 | 99 | 96 | 105 | 101 | 98 | 96 | 99 | 97 | 95 | 98 | 95 | 94 | 96 | 94 | 93 | 92 |
| 5 | 104 | 99 | 96 | 93 | 103 | 99 | 95 | 93 | 97 | 94 | 92 | 96 | 93 | 91 | 94 | 92 | 91 | 90 |
| 6 | 102 | 97 | 93 | 91 | 101 | 96 | 93 | 91 | 95 | 92 | 90 | 94 | 91 | 89 | 93 | 91 | 89 | 88 |
| 7 | 100 | 95 | 91 | 89 | 99 | 94 | 91 | 88 | 93 | 90 | 88 | 92 | 90 | 88 | 91 | 89 | 87 | 86 |
| 8 | 98 | 93 | 89 | 87 | 97 | 92 | 89 | 87 | 91 | 88 | 86 | 90 | 88 | 86 | 90 | 87 | 86 | 85 |
| 9 | 96 | 91 | 87 | 85 | 95 | 90 | 87 | 85 | 90 | 87 | 85 | 89 | 86 | 84 | 88 | 86 | 84 | 83 |
| 10 | 94 | 89 | 86 | 83 | 94 | 89 | 85 | 83 | 88 | 85 | 83 | 87 | 85 | 83 | 87 | 85 | 83 | 82 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 6503495 |
| 5° | 5184982 |
| 10° | 2251021 |
| 15° | 777743 |
| 20° | 318900 |
| 25° | 144039 |
| 30° | 57937 |
| 35° | 26982 |
| 40° | 14684 |
| 45° | 5442 |
| 50° | 3300 |
| 55° | 2408 |
| 60° | 1381 |
| 65° | 817 |
| 70° | 1010 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P278095

CATALOG NUMBER: LDA2B158030D010 EU2B15SP158030 2LBAD1WH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 791.2 | 55.0 |
| 10°-20° | 475.2 | 33.0 |
| 20°-30° | 130.8 | 9.1 |
| 30°-40° | 31.1 | 2.2 |
| 40°-50° | 7.7 | 0.5 |
| 50°-60° | 2.5 | 0.2 |
| 60°-70° | 0.9 | 0.1 |
| 70°-80° | 0.1 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1397.2 | 97.1 |
| 0°-40° | 1428.4 | 99.2 |
| 0°-60° | 1438.5 | 99.9 |
| 0°-90° | 1439.6 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1439.6 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-------|------|
| 0° | 13182 | |
| 5° | 10470 | 791 |
| 15° | 1523 | 475 |
| 25° | 265 | 131 |
| 35° | 45 | 31 |
| 45° | 8 | 8 |
| 55° | 3 | 3 |
| 65° | 1 | 1 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P278095

CATALOG NUMBER: LDA2B158030D010 EU2B15SP158030 2LBAD1WH

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|---------|
| 0° | 13182.0 |
| 1° | 13036.2 |
| 2° | 12687.0 |
| 3° | 12154.3 |
| 4° | 11402.6 |
| 5° | 10469.5 |
| 6° | 9330.2 |
| 7° | 8082.0 |
| 8° | 6770.6 |
| 9° | 5564.4 |
| 10° | 4493.3 |
| 11° | 3586.6 |
| 12° | 2854.7 |
| 13° | 2302.1 |
| 14° | 1862.6 |
| 15° | 1522.7 |
| 17.5° | 945.2 |
| 20° | 607.4 |
| 22.5° | 398.3 |
| 25° | 264.6 |
| 27.5° | 170.0 |
| 30° | 101.7 |
| 32.5° | 64.0 |
| 35° | 44.8 |
| 37.5° | 32.7 |
| 40° | 22.8 |
| 42.5° | 13.5 |
| 45° | 7.8 |
| 47.5° | 5.7 |
| 50° | 4.3 |
| 52.5° | 3.6 |
| 55° | 2.8 |
| 57.5° | 2.1 |
| 60° | 1.4 |
| 62.5° | 1.4 |
| 65° | 0.7 |
| 67.5° | 0.7 |
| 70° | 0.7 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |



TEST NUMBER: P278095

CATALOG NUMBER: LDA2B158030D010 EU2B15SP158030 2LBAD1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







| | | |
|-------|--|-----|
| 85° | | 0.0 |
| 87.5° | | 0.0 |



(END OF REPORT)