

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P495875

Luminaire Tested: **LDA2B109027R70D010 2LBDL1WH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P495875  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B109027R70D010 2LBDL1WH  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2700K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 741.5 lumens  
Efficiency: N/A  
Efficacy: 74.2 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P495875

CATALOG NUMBER: LDA2B109027R70D010 2LBDL1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P495875

CATALOG NUMBER: LDA2B109027R70D010 2LBDL1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82		87	84	81		85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		74	71	67	66
6	85	75	68	64	83	74	68	63	72	67	63		71	66	63		70	65	62	61
7	80	70	63	59	78	69	63	58	68	62	58		66	61	58		65	61	57	56
8	75	65	58	54	74	64	58	54	63	58	54		62	57	53		61	57	53	52
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57	53	49	48
10	68	57	51	46	66	57	50	46	56	50	46		55	50	46		54	49	46	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	293600
5°	291898
10°	289963
15°	284548
20°	274273
25°	262601
30°	250149
35°	206403
40°	134153
45°	70121
50°	32620
55°	11956
60°	1184
65°	934
70°	577
75°	762
80°	0
85°	0



TEST NUMBER: P495875

CATALOG NUMBER: LDA2B109027R70D010 2LBDL1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.7	7.5
10°-20°	156.6	21.1
20°-30°	222.2	30.0
30°-40°	207.8	28.0
40°-50°	83.6	11.3
50°-60°	14.6	2.0
60°-70°	0.7	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	434.5	58.6
0°-40°	642.3	86.6
0°-60°	740.5	99.9
0°-90°	741.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	741.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	595	
5°	589	56
15°	557	157
25°	482	222
35°	343	208
45°	100	84
55°	14	15
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P495875

CATALOG NUMBER: LDA2B109027R70D010 2LBDL1WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	595.1
1°	595.9
2°	594.7
3°	592.2
4°	591.0
5°	589.4
6°	582.8
7°	584.9
8°	579.2
9°	577.9
10°	578.8
11°	573.4
12°	572.2
13°	565.7
14°	563.2
15°	557.1
16°	553.4
17°	546.1
18°	537.5
19°	532.6
20°	522.4
21°	514.6
22.5°	500.3
23°	496.7
24°	489.7
25°	482.4
26°	476.6
27°	468.5
28°	460.3
29°	450.5
30°	439.1
32.5°	399.0
35°	342.7
37.5°	276.1
40°	208.3
42.5°	148.7
45°	100.5
47.5°	66.2
50°	42.5
52.5°	26.5
55°	13.9
57.5°	4.5
60°	1.2
62.5°	0.8
65°	0.8



TEST NUMBER: P495875

CATALOG NUMBER: LDA2B109027R70D010 2LBDL1WH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)