

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279584

Luminaire Tested: **LDA2B109040D010 EU2B10FL409040 2LBALD1WHH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P279584  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B109040D010 EU2B10FL409040 2LBALD1WHH  
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in  
ADJ spun Refl w/lens Self-Flanged, WHH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 989.0 lumens  
Efficiency: N/A  
Efficacy: 98.9 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P279584

CATALOG NUMBER: LDA2B109040D010 EU2B10FL409040 2LBALD1WHH

### Luminous Intensity Polar Plot





TEST NUMBER: P279584

CATALOG NUMBER: LDA2B109040D010 EU2B10FL409040 2LBALD1WHH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																																				
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																																				
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89																																				
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85																																				
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82																																				
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																																				
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																																				
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																																				
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72																																				
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69																																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1359804
5°	1331024
10°	1213155
15°	947726
20°	561094
25°	208600
30°	65172
35°	28970
40°	13460
45°	6349
50°	3454
55°	1978
60°	888
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P279584

CATALOG NUMBER: LDA2B109040D010 EU2B10FL409040 2LBALD1WHH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	248.4	25.1
10°-20°	494.1	50.0
20°-30°	202.3	20.5
30°-40°	33.5	3.4
40°-50°	7.9	0.8
50°-60°	2.1	0.2
60°-70°	0.5	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	944.8	95.5
0°-40°	978.3	98.9
0°-60°	988.4	99.9
0°-90°	989.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	989.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2756	
5°	2688	248
15°	1856	494
25°	383	202
35°	48	33
45°	9	8
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279584

CATALOG NUMBER: LDA2B109040D010 EU2B10FL409040 2LBALD1WHH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2756.2
1°	2746.6
2°	2733.9
3°	2722.6
4°	2707.6
5°	2687.6
6°	2658.1
7°	2619.5
8°	2564.6
9°	2497.9
10°	2421.6
11°	2333.1
12°	2233.2
13°	2119.2
14°	1992.6
15°	1855.5
17.5°	1471.4
20°	1068.7
22.5°	684.2
25°	383.2
27.5°	202.0
30°	114.4
32.5°	72.6
35°	48.1
37.5°	31.8
40°	20.9
42.5°	13.6
45°	9.1
47.5°	6.4
50°	4.5
52.5°	3.2
55°	2.3
57.5°	1.4
60°	0.9
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279584

CATALOG NUMBER: LDA2B109040D010 EU2B10FL409040 2LBALD1WHH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)