

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P497448

Luminaire Tested: **LDA2B158030R30D010 2LBD1MW**

Issue Date: 3/12/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P497448
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-14)
Test Lab: INNOVATION CENTER
Issue Date: 3/12/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B158030R30D010 2LBD1MW
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1341.6 lumens
Efficiency: N/A
Efficacy: 95.2 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.46
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P497448

CATALOG NUMBER: LDA2B158030R30D010 2LBD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P497448

CATALOG NUMBER: LDA2B158030R30D010 2LBD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	93
3	108	103	100	97	106	102	99	96	99	97	94	97	95	93	95	93	92	90
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	92	90	89	87
5	101	95	91	88	100	95	91	88	93	90	87	91	89	86	90	88	86	85
6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	88	85	83	82
7	96	89	85	82	95	89	85	82	87	84	81	86	83	81	85	83	81	80
8	93	86	82	79	92	86	82	79	85	81	79	84	81	79	83	81	78	77
9	90	84	80	77	90	83	80	77	83	79	77	82	79	76	81	78	76	75
10	88	81	77	75	87	81	77	75	80	77	75	80	77	74	79	76	74	73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2599967
5°	2479005
10°	2010403
15°	1228953
20°	536995
25°	200871
30°	83288
35°	38968
40°	18097
45°	8861
50°	4835
55°	1806
60°	691
65°	817
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P497448

CATALOG NUMBER: LDA2B158030R30D010 2LBD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	446.5	33.3
10°-20°	644.7	48.1
20°-30°	192.4	14.3
30°-40°	44.2	3.3
40°-50°	10.9	0.8
50°-60°	2.5	0.2
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1283.6	95.7
0°-40°	1327.9	99.0
0°-60°	1341.2	100.0
0°-90°	1341.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1341.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5270	
5°	5006	447
15°	2406	645
25°	369	192
35°	65	44
45°	13	11
55°	2	2
65°	1	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P497448

CATALOG NUMBER: LDA2B158030R30D010 2LBD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	5269.9
1°	5257.9
2°	5204.5
3°	5168.7
4°	5101.9
5°	5005.6
6°	4874.1
7°	4717.4
8°	4517.7
9°	4274.5
10°	4013.0
11°	3733.3
12°	3415.5
13°	3073.9
14°	2749.2
15°	2406.1
16°	2074.4
17°	1747.5
18°	1483.9
19°	1228.0
20°	1022.8
21°	828.8
22.5°	614.4
23°	553.9
24°	453.4
25°	369.0
26°	303.0
27°	252.4
28°	208.1
29°	174.3
30°	146.2
32.5°	95.6
35°	64.7
37.5°	42.9
40°	28.1
42.5°	18.3
45°	12.7
47.5°	9.1
50°	6.3
52.5°	4.2
55°	2.1
57.5°	1.4
60°	0.7
62.5°	0.7
65°	0.7



TEST NUMBER: P497448

CATALOG NUMBER: LDA2B158030R30D010 2LBD1MW

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)