

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P496011

Luminaire Tested: **LDA2B109030R45D010 2LBD1MW**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P496011
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-40)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B109030R45D010 2LBD1MW
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 880.7 lumens
Efficiency: N/A
Efficacy: 88.1 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 0.71 / 0.65
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P496011

CATALOG NUMBER: LDA2B109030R45D010 2LBD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P496011

CATALOG NUMBER: LDA2B109030R45D010 2LBD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86
4	101	95	90	87	100	94	90	86	92	88	85	90	87	84	88	86	84	82
5	97	90	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	78
6	94	86	81	78	92	86	81	77	84	80	77	83	79	76	82	78	76	75
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	78	75	73	71
8	87	79	74	71	86	78	74	70	77	73	70	76	73	70	76	72	70	68
9	84	76	71	67	83	75	70	67	74	70	67	73	70	67	73	69	67	66
10	81	73	68	65	80	72	68	64	71	67	64	71	67	64	70	67	64	63

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	874138
5°	860788
10°	803310
15°	701026
20°	536050
25°	311322
30°	132053
35°	54687
40°	24151
45°	12489
50°	6217
55°	1462
60°	888
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P496011

CATALOG NUMBER: LDA2B109030R45D010 2LBD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.7	18.4
10°-20°	374.3	42.5
20°-30°	261.7	29.7
30°-40°	64.8	7.4
40°-50°	15.0	1.7
50°-60°	2.5	0.3
60°-70°	0.5	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	797.8	90.6
0°-40°	862.6	97.9
0°-60°	880.1	99.9
0°-90°	880.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	880.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1772	
5°	1738	162
15°	1372	374
25°	572	262
35°	91	65
45°	18	15
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P496011

CATALOG NUMBER: LDA2B109030R45D010 2LBD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1771.8
1°	1768.0
2°	1767.1
3°	1761.6
4°	1745.8
5°	1738.1
6°	1722.4
7°	1699.8
8°	1672.1
9°	1643.5
10°	1603.5
11°	1570.7
12°	1530.6
13°	1478.6
14°	1425.8
15°	1372.5
16°	1313.7
17°	1243.8
18°	1173.1
19°	1100.2
20°	1021.0
21°	926.0
22.5°	802.8
23°	752.1
24°	660.9
25°	571.9
26°	488.3
27°	410.4
28°	341.7
29°	282.1
30°	231.8
32.5°	142.7
35°	90.8
37.5°	58.8
40°	37.5
42.5°	25.6
45°	17.9
47.5°	12.8
50°	8.1
52.5°	4.3
55°	1.7
57.5°	0.9
60°	0.9
62.5°	0.4
65°	0.4



TEST NUMBER: P496011

CATALOG NUMBER: LDA2B109030R45D010 2LBD1MW

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)