

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P497527

Luminaire Tested: **LDA2B158030R45D010 2LBDL1B**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P497527
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-42)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B158030R45D010 2LBDL1B
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1357.6 lumens
Efficiency: N/A
Efficacy: 96.3 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.65
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P497527
CATALOG NUMBER: LDA2B158030R45D010 2LBDL1B

Luminous Intensity Polar Plot





TEST NUMBER: P497527

CATALOG NUMBER: LDA2B158030R45D010 2LBDL1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	105	102	99	108	104	101	98	101	98	96		98	96	94		95	93	92	90
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91	89	87	86
4	101	95	90	86	99	94	89	86	91	88	85		90	86	84		88	85	83	82
5	97	90	85	81	95	89	84	81	87	83	80		86	82	80		84	81	79	78
6	93	86	81	77	92	85	80	77	84	79	76		82	79	76		81	78	75	74
7	90	82	77	73	88	81	76	73	80	76	73		79	75	72		78	74	72	71
8	86	78	73	70	85	78	73	70	77	72	69		76	72	69		75	71	69	68
9	83	75	70	66	82	74	70	66	74	69	66		73	69	66		72	68	66	65
10	80	72	67	64	79	71	67	64	71	66	63		70	66	63		69	66	63	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1345595
5°	1315919
10°	1220921
15°	1041196
20°	783862
25°	472563
30°	227874
35°	103292
40°	47530
45°	24490
50°	12971
55°	4817
60°	1381
65°	817
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P497527

CATALOG NUMBER: LDA2B158030R45D010 2LBDL1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	247.0	18.2
10°-20°	556.7	41.0
20°-30°	397.7	29.3
30°-40°	119.2	8.8
40°-50°	29.6	2.2
50°-60°	6.2	0.5
60°-70°	0.9	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1201.4	88.5
0°-40°	1320.6	97.3
0°-60°	1356.4	99.9
0°-90°	1357.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1357.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2727	
5°	2657	247
15°	2038	557
25°	868	398
35°	172	119
45°	35	30
55°	6	6
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P497527

CATALOG NUMBER: LDA2B158030R45D010 2LBDL1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	2727.4
1°	2732.3
2°	2726.0
3°	2702.8
4°	2685.9
5°	2657.1
6°	2628.3
7°	2597.3
8°	2546.7
9°	2498.9
10°	2437.1
11°	2375.2
12°	2297.2
13°	2213.5
14°	2135.5
15°	2038.5
16°	1943.6
17°	1836.1
18°	1734.1
19°	1609.0
20°	1493.0
21°	1364.4
22.5°	1172.5
23°	1107.8
24°	982.0
25°	868.1
26°	754.2
27°	650.2
28°	553.2
29°	473.8
30°	400.0
32.5°	262.9
35°	171.5
37.5°	112.5
40°	73.8
42.5°	49.9
45°	35.1
47.5°	25.3
50°	16.9
52.5°	10.5
55°	5.6
57.5°	2.8
60°	1.4
62.5°	1.4
65°	0.7



TEST NUMBER: P497527

CATALOG NUMBER: LDA2B158030R45D010 2LBDL1B

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)