

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P496039

Luminaire Tested: **LDA2B109030R60D010 2LBDL1GPH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P496039
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-55)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B109030R60D010 2LBDL1GPH
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 775.8 lumens
Efficiency: N/A
Efficacy: 77.6 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.86
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P496039

CATALOG NUMBER: LDA2B109030R60D010 2LBDL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P496039

CATALOG NUMBER: LDA2B109030R60D010 2LBDL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82
4	98	90	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71
6	88	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67
7	84	75	69	65	83	74	69	65	73	68	65	72	68	64	71	67	64	63
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59
9	76	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55
10	73	63	58	54	72	63	58	54	62	57	54	61	57	54	61	57	53	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	459122
5°	447158
10°	434844
15°	413312
20°	377650
25°	324278
30°	241319
35°	141657
40°	67495
45°	31537
50°	15734
55°	5505
60°	1283
65°	1051
70°	577
75°	762
80°	0
85°	0



TEST NUMBER: P496039

CATALOG NUMBER: LDA2B109030R60D010 2LBDL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.0	11.0
10°-20°	225.2	29.0
20°-30°	267.3	34.5
30°-40°	150.9	19.4
40°-50°	39.2	5.1
50°-60°	7.2	0.9
60°-70°	0.8	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	577.5	74.4
0°-40°	728.4	93.9
0°-60°	774.8	99.9
0°-90°	775.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	775.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	931	
5°	903	85
15°	809	225
25°	596	267
35°	235	151
45°	45	39
55°	6	7
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P496039

CATALOG NUMBER: LDA2B109030R60D010 2LBDL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	930.6
1°	931.1
2°	924.7
3°	919.1
4°	908.5
5°	902.9
6°	893.1
7°	885.9
8°	879.1
9°	874.4
10°	868.0
11°	855.6
12°	844.1
13°	837.7
14°	822.8
15°	809.2
16°	793.4
17°	774.7
18°	756.8
19°	735.5
20°	719.3
21°	697.1
22.5°	660.5
23°	654.1
24°	623.0
25°	595.7
26°	565.5
27°	530.5
28°	496.0
29°	462.3
30°	423.6
32.5°	326.0
35°	235.2
37.5°	160.6
40°	104.8
42.5°	68.6
45°	45.2
47.5°	30.7
50°	20.5
52.5°	12.8
55°	6.4
57.5°	2.6
60°	1.3
62.5°	0.9
65°	0.9



TEST NUMBER: P496039

CATALOG NUMBER: LDA2B109030R60D010 2LBDL1GPH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)