

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P497558

Luminaire Tested: **LDA2B158030R60D010 2LBDL1WHH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P497558  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-55)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B158030R60D010 2LBDL1WHH  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1279.7 lumens  
Efficiency: N/A  
Efficacy: 90.8 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.86  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P497558

CATALOG NUMBER: LDA2B158030R60D010 2LBDL1WHH

### Luminous Intensity Polar Plot





TEST NUMBER: P497558

CATALOG NUMBER: LDA2B158030R60D010 2LBDL1WHH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	85	83	82
4	98	91	85	81	96	89	84	81	87	83	80		85	82	79		83	80	78	76
5	93	85	79	75	91	84	79	75	82	78	74		81	77	73		79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	69	65	83	74	69	65	73	68	65		72	68	64		71	67	64	63
8	80	71	65	61	79	70	65	61	69	64	61		68	64	60		67	63	60	59
9	76	67	61	57	75	67	61	57	66	61	57		65	60	57		64	60	57	55
10	73	63	58	54	72	63	58	54	62	57	54		61	57	54		61	57	54	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	757409
5°	737669
10°	717343
15°	681821
20°	622942
25°	534947
30°	398039
35°	233686
40°	111354
45°	51980
50°	25866
55°	9032
60°	2072
65°	1634
70°	1010
75°	1334
80°	0
85°	0



TEST NUMBER: P497558

CATALOG NUMBER: LDA2B158030R60D010 2LBDL1WHH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	140.2	11.0
10°-20°	371.4	29.0
20°-30°	441.0	34.5
30°-40°	248.9	19.5
40°-50°	64.7	5.1
50°-60°	11.8	0.9
60°-70°	1.2	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	952.6	74.4
0°-40°	1201.5	93.9
0°-60°	1278.0	99.9
0°-90°	1279.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1279.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1535	
5°	1490	140
15°	1335	371
25°	983	441
35°	388	249
45°	74	65
55°	10	12
65°	1	1
75°	1	0
85°	0	0
90°	0	



TEST NUMBER: P497558

CATALOG NUMBER: LDA2B158030R60D010 2LBDL1WHH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1535.2
1°	1535.9
2°	1525.4
3°	1516.2
4°	1498.7
5°	1489.5
6°	1473.3
7°	1461.4
8°	1450.1
9°	1442.4
10°	1431.9
11°	1411.5
12°	1392.5
13°	1382.0
14°	1357.4
15°	1334.9
16°	1308.9
17°	1277.9
18°	1248.4
19°	1213.3
20°	1186.5
21°	1150.0
22.5°	1089.5
23°	1079.0
24°	1027.7
25°	982.7
26°	932.8
27°	875.2
28°	818.2
29°	762.7
30°	698.7
32.5°	537.7
35°	388.0
37.5°	265.0
40°	172.9
42.5°	113.2
45°	74.5
47.5°	50.6
50°	33.7
52.5°	21.1
55°	10.5
57.5°	4.2
60°	2.1
62.5°	1.4
65°	1.4



TEST NUMBER: P497558

CATALOG NUMBER: LDA2B158030R60D010 2LBDL1WHH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)