

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P496040

Luminaire Tested: **LDA2B109030R60D010 2LBDL1H**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P496040  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-55)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B109030R60D010 2LBDL1H  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 775.8 lumens  
Efficiency: N/A  
Efficacy: 77.6 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.86  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P496040  
CATALOG NUMBER: LDA2B109030R60D010 2LBDL1H

### Luminous Intensity Polar Plot





TEST NUMBER: P496040

CATALOG NUMBER: LDA2B109030R60D010 2LBDL1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	85	83	82
4	98	90	85	81	96	89	84	81	87	83	80		85	82	79		83	80	78	76
5	93	85	79	75	91	84	79	75	82	78	74		81	77	73		79	76	73	71
6	88	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	69	65	83	74	69	65	73	68	65		72	68	64		71	67	64	63
8	80	71	65	61	79	70	65	61	69	64	61		68	64	60		67	63	60	59
9	76	67	61	57	75	67	61	57	66	61	57		65	60	57		64	60	57	55
10	73	63	58	54	72	63	58	54	62	57	54		61	57	54		61	57	53	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	459122
5°	447158
10°	434844
15°	413312
20°	377650
25°	324278
30°	241319
35°	141657
40°	67495
45°	31537
50°	15734
55°	5505
60°	1283
65°	1051
70°	577
75°	762
80°	0
85°	0



TEST NUMBER: P496040

CATALOG NUMBER: LDA2B109030R60D010 2LBDL1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	85.0	11.0
10°-20°	225.2	29.0
20°-30°	267.3	34.5
30°-40°	150.9	19.4
40°-50°	39.2	5.1
50°-60°	7.2	0.9
60°-70°	0.8	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	577.5	74.4
0°-40°	728.4	93.9
0°-60°	774.8	99.9
0°-90°	775.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	775.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	931	
5°	903	85
15°	809	225
25°	596	267
35°	235	151
45°	45	39
55°	6	7
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P496040

CATALOG NUMBER: LDA2B109030R60D010 2LBDL1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	930.6
1°	931.1
2°	924.7
3°	919.1
4°	908.5
5°	902.9
6°	893.1
7°	885.9
8°	879.1
9°	874.4
10°	868.0
11°	855.6
12°	844.1
13°	837.7
14°	822.8
15°	809.2
16°	793.4
17°	774.7
18°	756.8
19°	735.5
20°	719.3
21°	697.1
22.5°	660.5
23°	654.1
24°	623.0
25°	595.7
26°	565.5
27°	530.5
28°	496.0
29°	462.3
30°	423.6
32.5°	326.0
35°	235.2
37.5°	160.6
40°	104.8
42.5°	68.6
45°	45.2
47.5°	30.7
50°	20.5
52.5°	12.8
55°	6.4
57.5°	2.6
60°	1.3
62.5°	0.9
65°	0.9



TEST NUMBER: P496040

CATALOG NUMBER: LDA2B109030R60D010 2LBDL1H

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)