

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P496051

Luminaire Tested: **LDA2B109030R65D010 2LBD1B**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P496051
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-66)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B109030R65D010 2LBD1B
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 862.8 lumens
Efficiency: N/A
Efficacy: 86.3 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.95
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P496051
CATALOG NUMBER: LDA2B109030R65D010 2LBD1B

Luminous Intensity Polar Plot





TEST NUMBER: P496051

CATALOG NUMBER: LDA2B109030R65D010 2LBD1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	111	108	106	111	109	106	104	104	103	101		101	99	98		97	96	95	93
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92	90	88	87
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87	84	82	80
4	97	89	84	79	95	88	83	79	86	82	78		84	80	77		82	79	76	75
5	92	83	78	73	90	82	77	73	81	76	72		79	75	72		77	74	71	69
6	87	78	72	68	86	77	72	67	76	71	67		74	70	66		73	69	66	65
7	83	73	67	63	81	73	67	63	71	66	62		70	65	62		69	65	62	60
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65	61	58	56
9	75	65	59	55	73	64	58	54	63	58	54		62	58	54		61	57	54	53
10	71	61	55	51	70	61	55	51	60	55	51		59	54	51		58	54	51	49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	468792
5°	431161
10°	412000
15°	395690
20°	364420
25°	337506
30°	309282
35°	227121
40°	107554
45°	35374
50°	11436
55°	1462
60°	888
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P496051

CATALOG NUMBER: LDA2B109030R65D010 2LBD1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.8	9.5
10°-20°	215.5	25.0
20°-30°	285.8	33.1
30°-40°	226.1	26.2
40°-50°	49.4	5.7
50°-60°	3.7	0.4
60°-70°	0.5	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	583.0	67.6
0°-40°	809.1	93.8
0°-60°	862.2	99.9
0°-90°	862.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	862.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	950	
5°	871	82
15°	775	215
25°	620	286
35°	377	226
45°	51	49
55°	2	4
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P496051

CATALOG NUMBER: LDA2B109030R65D010 2LBD1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	950.2
1°	945.1
2°	927.7
3°	908.5
4°	888.5
5°	870.6
6°	859.1
7°	847.5
8°	839.9
9°	828.4
10°	822.4
11°	813.0
12°	802.4
13°	793.0
14°	782.4
15°	774.7
16°	755.1
17°	745.3
18°	729.1
19°	714.2
20°	694.1
21°	678.0
22.5°	656.6
23°	650.7
24°	634.5
25°	620.0
26°	611.1
27°	596.1
28°	581.7
29°	564.2
30°	542.9
32.5°	468.7
35°	377.1
37.5°	268.9
40°	167.0
42.5°	94.2
45°	50.7
47.5°	27.3
50°	14.9
52.5°	6.4
55°	1.7
57.5°	0.9
60°	0.9
62.5°	0.4
65°	0.4



TEST NUMBER: P496051

CATALOG NUMBER: LDA2B109030R65D010 2LBD1B

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)