

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P496082

Luminaire Tested: **LDA2B109030R70D010 2LBD1WHH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P496082
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-79)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B109030R70D010 2LBD1WHH
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 835.6 lumens
Efficiency: N/A
Efficacy: 83.6 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.09
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P496082

CATALOG NUMBER: LDA2B109030R70D010 2LBD1WHH

Luminous Intensity Polar Plot





TEST NUMBER: P496082

CATALOG NUMBER: LDA2B109030R70D010 2LBD1WHH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85	82	80	78
4	95	87	81	77	93	86	81	76	84	79	75		82	78	74		80	76	74	72
5	90	81	75	70	88	80	74	70	78	73	69		76	72	68		75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70	66	62	61
7	80	70	63	59	79	69	63	59	68	62	58		67	62	58		66	61	58	56
8	76	65	59	54	74	65	59	54	64	58	54		62	57	54		61	57	54	52
9	71	61	55	50	70	61	54	50	60	54	50		59	54	50		58	53	50	48
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54	50	46	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	326507
5°	322901
10°	321274
15°	320148
20°	308714
25°	295971
30°	292989
35°	250249
40°	156179
45°	72214
50°	26173
55°	1806
60°	888
65°	1051
70°	577
75°	762
80°	0
85°	0



TEST NUMBER: P496082

CATALOG NUMBER: LDA2B109030R70D010 2LBD1WHH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.8	7.4
10°-20°	175.5	21.0
20°-30°	252.4	30.2
30°-40°	248.8	29.8
40°-50°	88.7	10.6
50°-60°	7.3	0.9
60°-70°	0.7	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	489.8	58.6
0°-40°	738.7	88.4
0°-60°	834.6	99.9
0°-90°	835.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	835.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	662	
5°	652	62
15°	627	176
25°	544	252
35°	416	249
45°	104	89
55°	2	7
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P496082

CATALOG NUMBER: LDA2B109030R70D010 2LBD1WHH

CANDELA DISTRIBUTION (FULL):

0°	
0°	661.8
1°	661.8
2°	660.5
3°	660.9
4°	655.4
5°	652.0
6°	647.3
7°	645.6
8°	643.4
9°	643.0
10°	641.3
11°	639.2
12°	639.2
13°	635.3
14°	630.2
15°	626.8
16°	620.0
17°	616.2
18°	604.2
19°	596.1
20°	588.0
21°	577.4
22.5°	562.5
23°	556.5
24°	551.0
25°	543.7
26°	539.5
27°	532.2
28°	531.4
29°	523.7
30°	514.3
32.5°	478.1
35°	415.5
37.5°	334.1
40°	242.5
42.5°	165.8
45°	103.5
47.5°	61.8
50°	34.1
52.5°	12.8
55°	2.1
57.5°	1.3
60°	0.9
62.5°	0.9
65°	0.9



TEST NUMBER: P496082

CATALOG NUMBER: LDA2B109030R70D010 2LBD1WHH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)