

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279597

Luminaire Tested: **LDA2B109050D010 EU2B10FL409050 2LBALD1B**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P279597  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B109050D010 EU2B10FL409050 2LBALD1B  
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in  
ADJ spun Refl w/lens Self-Flanged, B  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1016.0 lumens  
Efficiency: N/A  
Efficacy: 101.6 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P279597

CATALOG NUMBER: LDA2B109050D010 EU2B10FL409050 2LBALD1B

### Luminous Intensity Polar Plot





TEST NUMBER: P279597

CATALOG NUMBER: LDA2B109050D010 EU2B10FL409050 2LBALD1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100													100															
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96													96															
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92													92															
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89													89															
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85													85															
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82													82															
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79													79															
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77													77															
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74													74															
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72													72															
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69													69															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1397003
5°	1367474
10°	1246320
15°	973622
20°	576425
25°	214316
30°	66938
35°	29753
40°	13847
45°	6489
50°	3607
55°	1978
60°	888
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P279597

CATALOG NUMBER: LDA2B109050D010 EU2B10FL409050 2LBALD1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	255.2	25.1
10°-20°	507.6	50.0
20°-30°	207.9	20.5
30°-40°	34.4	3.4
40°-50°	8.1	0.8
50°-60°	2.2	0.2
60°-70°	0.5	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	970.7	95.5
0°-40°	1005.1	98.9
0°-60°	1015.4	99.9
0°-90°	1016.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1016.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2832	
5°	2761	255
15°	1906	508
25°	394	208
35°	49	34
45°	9	8
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279597

CATALOG NUMBER: LDA2B109050D010 EU2B10FL409050 2LBALD1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2831.6
1°	2821.8
2°	2808.7
3°	2797.1
4°	2781.7
5°	2761.2
6°	2730.8
7°	2691.2
8°	2634.8
9°	2566.2
10°	2487.8
11°	2396.9
12°	2294.3
13°	2177.2
14°	2047.1
15°	1906.2
17.5°	1511.6
20°	1097.9
22.5°	702.9
25°	393.7
27.5°	207.6
30°	117.5
32.5°	74.6
35°	49.4
37.5°	32.6
40°	21.5
42.5°	14.0
45°	9.3
47.5°	6.5
50°	4.7
52.5°	3.3
55°	2.3
57.5°	1.4
60°	0.9
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279597

CATALOG NUMBER: LDA2B109050D010 EU2B10FL409050 2LBALD1B

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)