

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278052

Luminaire Tested: **LDA2B109050D010 EU2B10SP159050 2LBAD1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P278052
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B109050D010 EU2B10SP159050 2LBAD1MW
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH SPOT OPTIC AND 2in
ADJ spun Refl, Self-Flanged, MW
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 950.6 lumens
Efficiency: N/A
Efficacy: 95.1 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P278052

CATALOG NUMBER: LDA2B109050D010 EU2B10SP159050 2LBAD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P278052

CATALOG NUMBER: LDA2B109050D010 EU2B10SP159050 2LBAD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	98
2	112	109	107	104	110	108	105	103	105	103	101	102	100	99	99	98	97	96
3	109	105	102	100	108	104	101	99	102	99	98	100	98	96	97	96	95	93
4	107	102	99	96	105	101	98	96	99	97	95	98	95	94	96	94	93	92
5	104	99	96	93	103	99	95	93	97	94	92	96	93	91	94	92	91	90
6	102	97	93	91	101	96	93	91	95	92	90	94	91	89	93	91	89	88
7	100	95	91	89	99	94	91	88	93	90	88	92	90	88	91	89	87	86
8	98	93	89	87	97	92	89	87	91	88	86	90	88	86	90	87	86	85
9	96	91	87	85	95	90	87	85	90	87	85	89	86	84	88	86	84	83
10	94	89	86	83	94	89	85	83	88	85	83	87	85	83	87	85	83	82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4294270
5°	3423638
10°	1486386
15°	513524
20°	210535
25°	95100
30°	38283
35°	17828
40°	9661
45°	3628
50°	2149
55°	1634
60°	888
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P278052

CATALOG NUMBER: LDA2B109050D010 EU2B10SP159050 2LBAD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	522.5	55.0
10°-20°	313.8	33.0
20°-30°	86.4	9.1
30°-40°	20.6	2.2
40°-50°	5.1	0.5
50°-60°	1.7	0.2
60°-70°	0.6	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	922.6	97.1
0°-40°	943.1	99.2
0°-60°	949.9	99.9
0°-90°	950.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	950.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8704	
5°	6913	522
15°	1005	314
25°	175	86
35°	30	21
45°	5	5
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278052

CATALOG NUMBER: LDA2B109050D010 EU2B10SP159050 2LBAD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	8704.1
1°	8607.8
2°	8377.3
3°	8025.5
4°	7529.2
5°	6913.0
6°	6160.7
7°	5336.6
8°	4470.6
9°	3674.2
10°	2967.0
11°	2368.2
12°	1885.0
13°	1520.1
14°	1229.9
15°	1005.4
17.5°	624.1
20°	401.0
22.5°	263.0
25°	174.7
27.5°	112.2
30°	67.2
32.5°	42.3
35°	29.6
37.5°	21.6
40°	15.0
42.5°	8.9
45°	5.2
47.5°	3.8
50°	2.8
52.5°	2.3
55°	1.9
57.5°	1.4
60°	0.9
62.5°	0.9
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P278052

CATALOG NUMBER: LDA2B109050D010 EU2B10SP159050 2LBAD1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)