

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279690

Luminaire Tested: **LDA2B158035D010 EU2B15FL408035 2LBALD1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279690
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B158035D010 EU2B15FL408035 2LBALD1LI
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl w/lens Self-Flanged, H
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1557.2 lumens
Efficiency: N/A
Efficacy: 110.4 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279690

CATALOG NUMBER: LDA2B158035D010 EU2B15FL408035 2LBALD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P279690

CATALOG NUMBER: LDA2B158035D010 EU2B15FL408035 2LBALD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																											
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																											
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89																											
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85																											
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82																											
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79																											
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																											
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																											
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72																											
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2141239
5°	2095982
10°	1910309
15°	1492355
20°	883564
25°	328470
30°	102657
35°	45653
40°	21189
45°	9977
50°	5449
55°	3097
60°	1381
65°	817
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P279690

CATALOG NUMBER: LDA2B158035D010 EU2B15FL408035 2LBALD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	391.2	25.1
10°-20°	778.0	50.0
20°-30°	318.6	20.5
30°-40°	52.7	3.4
40°-50°	12.5	0.8
50°-60°	3.3	0.2
60°-70°	0.8	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1487.8	95.5
0°-40°	1540.5	98.9
0°-60°	1556.3	99.9
0°-90°	1557.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1557.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4340	
5°	4232	391
15°	2922	778
25°	603	319
35°	76	53
45°	14	12
55°	4	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279690

CATALOG NUMBER: LDA2B158035D010 EU2B15FL408035 2LBALD1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4340.1
1°	4325.1
2°	4305.1
3°	4287.2
4°	4263.6
5°	4232.2
6°	4185.7
7°	4124.9
8°	4038.4
9°	3933.3
10°	3813.2
11°	3673.8
12°	3516.6
13°	3337.1
14°	3137.7
15°	2921.8
17.5°	2317.0
20°	1682.9
22.5°	1077.3
25°	603.4
27.5°	318.1
30°	180.2
32.5°	114.4
35°	75.8
37.5°	50.0
40°	32.9
42.5°	21.4
45°	14.3
47.5°	10.0
50°	7.1
52.5°	5.0
55°	3.6
57.5°	2.1
60°	1.4
62.5°	0.7
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279690

CATALOG NUMBER: LDA2B158035D010 EU2B15FL408035 2LBALD1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)