

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278021

Luminaire Tested: **LDA2B109027D010 EU2B10SP159027 2LBAD1B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P278021
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B109027D010 EU2B10SP159027 2LBAD1B
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH SPOT OPTIC AND 2in
ADJ spun Refl, Self-Flanged, B
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 836.4 lumens
Efficiency: N/A
Efficacy: 83.6 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P278021

CATALOG NUMBER: LDA2B109027D010 EU2B10SP159027 2LBAD1B

Luminous Intensity Polar Plot





TEST NUMBER: P278021

CATALOG NUMBER: LDA2B109027D010 EU2B10SP159027 2LBAD1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	98	97	96	95	94	93	92	91	90	89	88	87	86	85	84	83	82																				
2	112	109	107	104	110	108	105	103	105	103	101	102	100	99	99	98	97	96	95	94	93	92	91	90	89	88	87	86	85	84	83	82																						
3	109	105	102	100	108	104	101	99	102	99	98	100	98	96	97	96	95	94	93	92	91	90	89	88	87	86	85	84	83	82																								
4	107	102	99	96	105	101	98	96	99	97	95	98	95	94	96	94	93	92	91	90	89	88	87	86	85	84	83	82																										
5	104	99	96	93	103	99	95	93	97	94	92	96	93	91	94	92	91	90	89	88	87	86	85	84	83	82																												
6	102	97	93	91	101	96	93	91	95	92	90	94	91	89	93	91	89	88	87	86	85	84	83	82																														
7	100	95	91	89	99	94	91	88	93	90	88	92	90	88	91	89	87	86	85	84	83	82																																
8	98	93	89	87	97	92	89	87	91	88	86	90	88	86	90	87	86	85	84	83	82																																	
9	96	91	87	85	95	90	87	85	90	87	85	89	86	84	88	86	84	83	82																																			
10	94	89	86	83	94	89	85	83	88	85	83	87	85	83	87	85	83	82																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3778806
5°	3012732
10°	1307939
15°	451874
20°	185281
25°	83669
30°	33668
35°	15659
40°	8501
45°	3140
50°	1919
55°	1462
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P278021

CATALOG NUMBER: LDA2B109027D010 EU2B10SP159027 2LBAD1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	459.7	55.0
10°-20°	276.1	33.0
20°-30°	76.0	9.1
30°-40°	18.1	2.2
40°-50°	4.5	0.5
50°-60°	1.5	0.2
60°-70°	0.5	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	811.9	97.1
0°-40°	829.9	99.2
0°-60°	835.9	99.9
0°-90°	836.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	836.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7659	
5°	6083	460
15°	885	276
25°	154	76
35°	26	18
45°	4	4
55°	2	1
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278021

CATALOG NUMBER: LDA2B109027D010 EU2B10SP159027 2LBAD1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	7659.3
1°	7574.6
2°	7371.7
3°	7062.2
4°	6625.4
5°	6083.3
6°	5421.3
7°	4696.0
8°	3934.0
9°	3233.2
10°	2610.8
11°	2084.0
12°	1658.7
13°	1337.6
14°	1082.3
15°	884.7
17.5°	549.2
20°	352.9
22.5°	231.4
25°	153.7
27.5°	98.8
30°	59.1
32.5°	37.2
35°	26.0
37.5°	19.0
40°	13.2
42.5°	7.9
45°	4.5
47.5°	3.3
50°	2.5
52.5°	2.1
55°	1.7
57.5°	1.2
60°	0.8
62.5°	0.8
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P278021

CATALOG NUMBER: LDA2B109027D010 EU2B10SP159027 2LBAD1B

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)