

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280433

Luminaire Tested: **LDA2B109027D010 EU2B10WFL559027 2LBALD1GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280433
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B109027D010 EU2B10WFL559027 2LBALD1GPH
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl w/lens Self-Flanged, GPH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 875.5 lumens
Efficiency: N/A
Efficacy: 87.6 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280433

CATALOG NUMBER: LDA2B109027D010 EU2B10WFL559027 2LBALD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P280433

CATALOG NUMBER: LDA2B109027D010 EU2B10WFL559027 2LBALD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	747739
5°	732469
10°	681173
15°	594736
20°	492368
25°	376591
30°	206055
35°	76309
40°	26406
45°	11931
50°	5603
55°	2752
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P280433

CATALOG NUMBER: LDA2B109027D010 EU2B10WFL559027 2LBALD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.4	15.7
10°-20°	321.8	36.8
20°-30°	304.2	34.7
30°-40°	93.6	10.7
40°-50°	14.8	1.7
50°-60°	3.1	0.4
60°-70°	0.4	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	763.4	87.2
0°-40°	857.1	97.9
0°-60°	875.0	99.9
0°-90°	875.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	875.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1516	
5°	1479	137
15°	1164	322
25°	692	304
35°	127	94
45°	17	15
55°	3	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280433

CATALOG NUMBER: LDA2B109027D010 EU2B10WFL559027 2LBALD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1515.6
1°	1509.9
2°	1503.0
3°	1497.3
4°	1490.0
5°	1479.0
6°	1464.8
7°	1445.7
8°	1420.2
9°	1390.5
10°	1359.7
11°	1325.6
12°	1289.4
13°	1250.1
14°	1209.1
15°	1164.4
17.5°	1046.2
20°	937.8
22.5°	827.8
25°	691.8
27.5°	527.8
30°	361.7
32.5°	222.1
35°	126.7
37.5°	70.6
40°	41.0
42.5°	25.6
45°	17.1
47.5°	11.4
50°	7.3
52.5°	4.9
55°	3.2
57.5°	2.0
60°	0.8
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280433

CATALOG NUMBER: LDA2B109027D010 EU2B10WFL559027 2LBALD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)