

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P497794

Luminaire Tested: **LDA2B158035R65D010 2LBDL1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P497794  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-68)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B158035R65D010 2LBDL1MMS  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3500K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1330.3 lumens  
Efficiency: N/A  
Efficacy: 94.4 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.94  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P497794

CATALOG NUMBER: LDA2B158035R65D010 2LBDL1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P497794

CATALOG NUMBER: LDA2B158035R65D010 2LBDL1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97	96	95	93
2	108	103	99	95	105	101	97	94	98	95	92		95	92	90		92	90	88	87
3	102	96	90	86	100	94	89	86	91	88	84		89	86	83		87	84	82	80
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82	78	76	74
5	92	83	77	73	90	82	76	72	80	75	72		79	74	71		77	73	70	69
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73	69	65	64
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68	64	61	60
8	78	68	62	58	77	68	62	58	67	61	58		66	61	57		65	60	57	56
9	74	64	58	54	73	64	58	54	63	58	54		62	57	54		61	57	53	52
10	71	61	55	51	70	60	54	51	59	54	50		59	54	50		58	53	50	49

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	696035
5°	666998
10°	635183
15°	603674
20°	561619
25°	518453
30°	449823
35°	322764
40°	175307
45°	74865
50°	32160
55°	11612
60°	2072
65°	1634
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P497794

CATALOG NUMBER: LDA2B158035R65D010 2LBDL1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	126.1	9.5
10°-20°	331.1	24.9
20°-30°	432.9	32.5
30°-40°	329.3	24.8
40°-50°	95.2	7.2
50°-60°	14.3	1.1
60°-70°	1.2	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	890.0	66.9
0°-40°	1219.4	91.7
0°-60°	1328.9	99.9
0°-90°	1330.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1330.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1411	
5°	1347	126
15°	1182	331
25°	952	433
35°	536	329
45°	107	95
55°	14	14
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P497794

CATALOG NUMBER: LDA2B158035R65D010 2LBDL1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1410.8
1°	1405.8
2°	1398.0
3°	1382.4
4°	1365.3
5°	1346.8
6°	1329.1
7°	1313.4
8°	1298.5
9°	1285.0
10°	1267.9
11°	1253.0
12°	1237.4
13°	1221.7
14°	1204.7
15°	1181.9
16°	1164.9
17°	1144.3
18°	1113.0
19°	1096.7
20°	1069.7
21°	1045.5
22.5°	1008.5
23°	994.3
24°	972.3
25°	952.4
26°	926.1
27°	896.9
28°	865.0
29°	830.8
30°	789.6
32.5°	676.6
35°	535.9
37.5°	395.2
40°	272.2
42.5°	172.7
45°	107.3
47.5°	66.8
50°	41.9
52.5°	24.9
55°	13.5
57.5°	5.0
60°	2.1
62.5°	1.4
65°	1.4



TEST NUMBER: P497794

CATALOG NUMBER: LDA2B158035R65D010 2LBDL1MMS

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)