

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280431

Luminaire Tested: **LDA2B109027D010 EU2B10WFL559027 2LBALD1WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280431
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B109027D010 EU2B10WFL559027 2LBALD1WH
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl w/lens Self-Flanged, WH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 885.4 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280431

CATALOG NUMBER: LDA2B109027D010 EU2B10WFL559027 2LBALD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P280431

CATALOG NUMBER: LDA2B109027D010 EU2B10WFL559027 2LBALD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	756176
5°	740740
10°	688837
15°	601427
20°	497933
25°	380837
30°	208391
35°	77153
40°	26728
45°	12001
50°	5680
55°	2838
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P280431

CATALOG NUMBER: LDA2B109027D010 EU2B10WFL559027 2LBALD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.0	15.7
10°-20°	325.5	36.8
20°-30°	307.6	34.7
30°-40°	94.7	10.7
40°-50°	15.0	1.7
50°-60°	3.2	0.4
60°-70°	0.4	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	772.1	87.2
0°-40°	866.7	97.9
0°-60°	884.9	99.9
0°-90°	885.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	885.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1533	
5°	1496	139
15°	1178	325
25°	700	308
35°	128	95
45°	17	15
55°	3	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280431

CATALOG NUMBER: LDA2B109027D010 EU2B10WFL559027 2LBALD1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1532.7
1°	1526.9
2°	1520.0
3°	1514.2
4°	1506.8
5°	1495.7
6°	1481.4
7°	1462.1
8°	1436.2
9°	1406.2
10°	1375.0
11°	1340.5
12°	1304.0
13°	1264.2
14°	1222.7
15°	1177.5
17.5°	1058.1
20°	948.4
22.5°	837.2
25°	699.6
27.5°	533.7
30°	365.8
32.5°	224.6
35°	128.1
37.5°	71.4
40°	41.5
42.5°	25.9
45°	17.2
47.5°	11.5
50°	7.4
52.5°	4.9
55°	3.3
57.5°	2.1
60°	0.8
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280431

CATALOG NUMBER: LDA2B109027D010 EU2B10WFL559027 2LBALD1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)