

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P496119

Luminaire Tested: **LDA2B109035R20D010 2LBDC1MMS-30DEG TILT**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P496119  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B109035R20D010 2LBDC1MMS-30DEG TILT  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3500K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 577.0 lumens  
Efficiency: N/A  
Efficacy: 57.7 lumens/watt  
Spacing Criteria (0/90/45): 2.56 / 0.56 / 1.2  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P496119

CATALOG NUMBER: LDA2B109035R20D010 2LBDC1MMS-30DEG TILT

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°



TEST NUMBER: P496119

CATALOG NUMBER: LDA2B109035R20D010 2LBDC1MMS-30DEG TILT

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91					91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82					82			
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74					74			
4	92	83	76	71	90	82	75	70	79	74	70	77	73	69	75	71	68	66					66			
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59					59			
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53					53			
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48					48			
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43					43			
9	64	53	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38					38			
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34					34			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	9177	9177	9177
5°	17532	8122	5893
10°	41881	7114	4008
15°	244044	5669	1583
20°	1217270	3465	473
25°	2219592	1198	0
30°	2603347	0	0
35°	2278559	0	0
40°	1682678	0	0
45°	606527	0	0
50°	126336	0	0
55°	28901	344	0
60°	9177	395	0
65°	2101	1051	0
70°	0	1298	577
75°	0	1716	0
80°	0	2557	0
85°	0	5095	0



TEST NUMBER: P496119

CATALOG NUMBER: LDA2B109035R20D010 2LBDC1MMS-30DEG TILT

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	2.1	0.4
10°-20°	31.7	5.5
20°-30°	213.7	37.0
30°-40°	249.6	43.3
40°-50°	72.8	12.6
50°-60°	4.8	0.8
60°-70°	0.9	0.2
70°-80°	0.7	0.1
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	247.5	42.9
0°-40°	497.1	86.2
0°-60°	574.8	99.6
0°-90°	577.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	577.0	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	19	19	19	19	19	
5°	35	26	16	14	12	5
15°	478	54	11	6	3	249
25°	4077	84	2	0	0	1805
35°	3783	45	0	0	0	2324
45°	869	9	0	0	0	801
55°	34	2	0	0	0	43
65°	2	1	1	1	0	3
75°	0	1	1	1	0	0
85°	0	1	1	1	0	0
90°	0	0	0	0	0	



TEST NUMBER: P496119

CATALOG NUMBER: LDA2B109035R20D010 2LBDC1MMS-30DEG TILT

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	18.6	18.6	18.6	18.6	18.6	18.6	18.6	18.6	18.6
2.5°	23.9	23.9	21.2	19.0	17.3	16.4	15.9	15.0	14.6
5°	35.4	31.0	25.7	19.9	16.4	15.0	13.7	12.4	11.9
7.5°	51.8	45.1	31.0	20.3	15.5	13.3	11.9	10.6	9.7
10°	83.6	65.0	38.0	20.3	14.2	11.5	9.7	8.4	8.0
12.5°	154.4	99.5	45.6	19.9	12.8	9.7	7.5	6.6	5.3
15°	477.8	206.1	54.0	19.0	11.1	7.5	5.8	3.5	3.1
17.5°	1235.6	481.3	60.2	16.8	8.8	5.3	2.7	2.2	2.2
20°	2318.5	872.8	69.0	14.6	6.6	3.5	1.8	1.3	0.9
21°	2645.0	1067.9	73.4	13.7	5.8	2.2	1.3	0.4	0.4
22°	3152.4	1280.7	77.0	12.8	4.9	1.3	0.9	0.4	0.0
23°	3513.8	1416.5	80.5	11.5	3.5	1.3	0.4	0.0	0.0
24°	3875.3	1589.5	82.7	10.6	3.1	0.9	0.4	0.0	0.0
25°	4077.4	1733.7	83.6	9.7	2.2	0.4	0.0	0.0	0.0
26°	4243.8	1830.1	84.1	8.8	1.3	0.0	0.0	0.0	0.0
27°	4386.2	1942.1	83.2	8.0	1.3	0.0	0.0	0.0	0.0
28°	4467.2	1960.6	81.8	7.1	0.4	0.0	0.0	0.0	0.0
29°	4502.1	1938.1	77.9	6.2	0.4	0.0	0.0	0.0	0.0
30°	4569.8	1916.8	73.9	5.8	0.0	0.0	0.0	0.0	0.0
31°	4507.4	1846.5	69.0	4.9	0.0	0.0	0.0	0.0	0.0
32°	4263.2	1787.2	63.3	4.0	0.0	0.0	0.0	0.0	0.0
33°	4190.2	1665.6	57.1	3.5	0.0	0.0	0.0	0.0	0.0
34°	4052.7	1484.6	51.8	3.1	0.0	0.0	0.0	0.0	0.0
35°	3783.2	1335.1	45.1	2.7	0.0	0.0	0.0	0.0	0.0
36°	3595.2	1164.3	39.4	2.2	0.0	0.0	0.0	0.0	0.0
37°	3398.4	1015.3	34.9	1.8	0.0	0.0	0.0	0.0	0.0
38°	3153.7	858.7	29.6	1.3	0.0	0.0	0.0	0.0	0.0
39°	2868.8	709.6	25.2	1.3	0.0	0.0	0.0	0.0	0.0
40°	2612.7	572.0	21.7	0.9	0.0	0.0	0.0	0.0	0.0
42.5°	1612.5	326.5	12.8	0.9	0.0	0.0	0.0	0.0	0.0
45°	869.3	198.2	9.3	0.4	0.0	0.0	0.0	0.0	0.0
47.5°	400.4	92.5	6.6	0.4	0.0	0.0	0.0	0.0	0.0
50°	164.6	41.1	4.9	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	59.3	23.0	3.1	0.0	0.0	0.4	0.0	0.0	0.0
55°	33.6	13.3	1.8	0.4	0.4	0.4	0.4	0.0	0.0
57.5°	15.9	7.5	0.4	0.4	0.4	0.4	0.4	0.0	0.0
60°	9.3	4.0	0.4	0.4	0.4	0.9	0.4	0.0	0.0
62.5°	4.4	1.3	0.4	0.9	0.9	0.9	0.9	0.4	0.0
65°	1.8	0.4	0.9	0.9	0.9	1.3	0.9	0.4	0.0
67.5°	0.4	0.4	0.9	0.9	0.9	1.3	0.9	0.4	0.4
70°	0.0	0.4	0.9	0.9	0.9	1.3	0.9	0.4	0.4
72.5°	0.0	0.4	0.9	0.9	0.9	1.3	0.9	0.4	0.4
75°	0.0	0.4	0.9	0.9	0.9	0.9	0.9	0.4	0.0
77.5°	0.0	0.4	0.9	0.9	0.9	0.9	0.9	0.4	0.0
80°	0.0	0.4	0.9	0.9	0.9	0.9	0.9	0.4	0.0



TEST NUMBER: P496119

CATALOG NUMBER: LDA2B109035R20D010 2LBDC1MMS-30DEG TILT

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
82.5°	0.0	0.4	0.9	0.9	0.9	0.9	0.9	0.4	0.0
85°	0.0	0.4	0.9	0.9	0.9	0.9	0.9	0.4	0.0
87.5°	0.0	0.4	0.9	0.9	0.9	0.9	0.4	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)