

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P496126

Luminaire Tested: **LDA2B109035R20D010 2LBDL1LI**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P496126
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-3)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B109035R20D010 2LBDL1LI
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 850.0 lumens
Efficiency: N/A
Efficacy: 85.0 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.34
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P496126
CATALOG NUMBER: LDA2B109035R20D010 2LBDL1LI

Luminous Intensity Polar Plot





TEST NUMBER: P496126

CATALOG NUMBER: LDA2B109035R20D010 2LBDL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97
2	112	109	106	104	110	107	105	102	104	102	100	101	100	98	98	97	96	95
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	97	95	94	92
4	106	101	98	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90
5	103	98	94	92	102	97	94	91	96	93	90	94	92	90	93	91	89	88
6	101	95	91	89	100	95	91	88	93	90	88	92	89	87	91	89	87	86
7	98	93	89	86	97	92	89	86	91	88	86	90	87	85	89	87	85	84
8	96	90	87	84	95	90	86	84	89	86	84	88	85	83	87	85	83	82
9	94	88	85	82	93	88	84	82	87	84	82	86	84	82	86	83	81	81
10	92	86	83	80	91	86	83	80	85	82	80	85	82	80	84	82	80	79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2809991
5°	2375102
10°	1447160
15°	595400
20°	214368
25°	85955
30°	39080
35°	18370
40°	9661
45°	5233
50°	3070
55°	1548
60°	888
65°	467
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P496126

CATALOG NUMBER: LDA2B109035R20D010 2LBDL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	395.6	46.5
10°-20°	342.2	40.3
20°-30°	82.5	9.7
30°-40°	21.1	2.5
40°-50°	6.4	0.7
50°-60°	1.8	0.2
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	820.2	96.5
0°-40°	841.4	99.0
0°-60°	849.6	100.0
0°-90°	850.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	850.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5696	
5°	4796	396
15°	1166	342
25°	158	82
35°	30	21
45°	8	6
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P496126

CATALOG NUMBER: LDA2B109035R20D010 2LBDL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	5695.6
1°	5646.1
2°	5528.0
3°	5348.4
4°	5117.0
5°	4795.8
6°	4464.1
7°	4097.8
8°	3717.3
9°	3290.4
10°	2888.7
11°	2468.9
12°	2100.9
13°	1752.7
14°	1433.3
15°	1165.7
16°	944.5
17°	762.7
18°	615.4
19°	506.1
20°	408.3
22.5°	251.7
25°	157.9
27.5°	102.6
30°	68.6
32.5°	45.1
35°	30.5
37.5°	21.2
40°	15.0
42.5°	10.6
45°	7.5
47.5°	5.8
50°	4.0
52.5°	2.7
55°	1.8
57.5°	1.3
60°	0.9
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0



TEST NUMBER: P496126

CATALOG NUMBER: LDA2B109035R20D010 2LBDL1LI

CANDELA DISTRIBUTION (continued):

	0°
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)