

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P497806

Luminaire Tested: **LDA2B158035R70D010 2LBD1MB**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P497806
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-79)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B158035R70D010 2LBD1MB
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1393.7 lumens
Efficiency: N/A
Efficacy: 98.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.09
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P497806

CATALOG NUMBER: LDA2B158035R70D010 2LBD1MB

Luminous Intensity Polar Plot





TEST NUMBER: P497806

CATALOG NUMBER: LDA2B158035R70D010 2LBD1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93					93			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85					85			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	82	80	78					78			
4	95	87	81	77	93	86	81	76	84	79	75	82	78	74	80	76	74	72					72			
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66					66			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61					61			
7	80	70	63	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56					56			
8	76	65	59	54	74	65	59	54	64	58	54	62	57	54	61	57	54	52					52			
9	71	61	55	50	70	61	54	50	60	54	50	59	54	50	58	53	50	48					48			
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45					45			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	544573
5°	538531
10°	535840
15°	534006
20°	514944
25°	493684
30°	488733
35°	417382
40°	260449
45°	120496
50°	43673
55°	3097
60°	1381
65°	1634
70°	1010
75°	1334
80°	0
85°	0



TEST NUMBER: P497806

CATALOG NUMBER: LDA2B158035R70D010 2LBD1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.2	7.4
10°-20°	292.8	21.0
20°-30°	421.0	30.2
30°-40°	415.0	29.8
40°-50°	147.9	10.6
50°-60°	12.2	0.9
60°-70°	1.1	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	817.0	58.6
0°-40°	1232.0	88.4
0°-60°	1392.1	99.9
0°-90°	1393.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1393.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1104	
5°	1087	103
15°	1046	293
25°	907	421
35°	693	415
45°	173	148
55°	4	12
65°	1	1
75°	1	0
85°	0	0
90°	0	



TEST NUMBER: P497806

CATALOG NUMBER: LDA2B158035R70D010 2LBD1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	1103.8
1°	1103.8
2°	1101.6
3°	1102.3
4°	1093.1
5°	1087.4
6°	1079.6
7°	1076.8
8°	1073.2
9°	1072.5
10°	1069.6
11°	1066.1
12°	1066.1
13°	1059.7
14°	1051.2
15°	1045.5
16°	1034.1
17°	1027.7
18°	1007.8
19°	994.3
20°	980.8
21°	963.0
22.5°	938.2
23°	928.2
24°	919.0
25°	906.9
26°	899.8
27°	887.7
28°	886.3
29°	873.5
30°	857.9
32.5°	797.4
35°	693.0
37.5°	557.2
40°	404.4
42.5°	276.5
45°	172.7
47.5°	103.1
50°	56.9
52.5°	21.3
55°	3.6
57.5°	2.1
60°	1.4
62.5°	1.4
65°	1.4



TEST NUMBER: P497806

CATALOG NUMBER: LDA2B158035R70D010 2LBD1MB

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)