

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P496226

Luminaire Tested: **LDA2B109035R45D010 2LBD1MMS**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P496226  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-40)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B109035R45D010 2LBD1MMS  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3500K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 914.3 lumens  
Efficiency: N/A  
Efficacy: 91.4 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 0.71 / 0.65  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P496226

CATALOG NUMBER: LDA2B109035R45D010 2LBD1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P496226

CATALOG NUMBER: LDA2B109035R45D010 2LBD1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86
4	101	95	90	87	100	94	90	86	92	88	85	90	87	84	88	86	84	82
5	97	90	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	78
6	94	86	81	78	92	86	81	77	84	80	77	83	79	76	82	78	76	75
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	78	75	73	71
8	87	79	74	71	86	78	74	70	77	73	70	76	73	70	76	72	70	68
9	84	76	71	67	83	75	70	67	74	70	67	73	70	67	73	69	67	66
10	81	73	68	65	80	72	68	64	71	67	64	71	67	64	70	67	64	63

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	907490
5°	893672
10°	833969
15°	727790
20°	556474
25°	323189
30°	137123
35°	56735
40°	25053
45°	12978
50°	6447
55°	1548
60°	888
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P496226

CATALOG NUMBER: LDA2B109035R45D010 2LBD1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	167.9	18.4
10°-20°	388.6	42.5
20°-30°	271.7	29.7
30°-40°	67.3	7.4
40°-50°	15.6	1.7
50°-60°	2.6	0.3
60°-70°	0.5	0.0
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	828.3	90.6
0°-40°	895.5	97.9
0°-60°	913.7	99.9
0°-90°	914.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	914.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1839	
5°	1804	168
15°	1425	389
25°	594	272
35°	94	67
45°	19	16
55°	2	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P496226

CATALOG NUMBER: LDA2B109035R45D010 2LBD1MMS

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1839.4
1°	1835.4
2°	1834.6
3°	1828.8
4°	1812.4
5°	1804.5
6°	1788.1
7°	1764.7
8°	1735.9
9°	1706.3
10°	1664.7
11°	1630.6
12°	1589.0
13°	1535.1
14°	1480.2
15°	1424.9
16°	1363.9
17°	1291.3
18°	1217.9
19°	1142.2
20°	1059.9
21°	961.3
22.5°	833.4
23°	780.8
24°	686.1
25°	593.7
26°	507.0
27°	426.0
28°	354.8
29°	292.9
30°	240.7
32.5°	148.2
35°	94.2
37.5°	61.0
40°	38.9
42.5°	26.5
45°	18.6
47.5°	13.3
50°	8.4
52.5°	4.4
55°	1.8
57.5°	0.9
60°	0.9
62.5°	0.4
65°	0.4



TEST NUMBER: P496226

CATALOG NUMBER: LDA2B109035R45D010 2LBD1MMS

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)