

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279698

Luminaire Tested: **LDA2B158040D010 EU2B15FL408040 2LBAD1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279698
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B158040D010 EU2B15FL408040 2LBAD1H
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl, Self-Flanged, H
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1630.3 lumens
Efficiency: N/A
Efficacy: 115.6 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279698

CATALOG NUMBER: LDA2B158040D010 EU2B15FL408040 2LBAD1H

Luminous Intensity Polar Plot





TEST NUMBER: P279698

CATALOG NUMBER: LDA2B158040D010 EU2B15FL408040 2LBAD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92			
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89			
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85			
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	84	82			
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74			
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72			
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2241787
5°	2194338
10°	2000033
15°	1562381
20°	925041
25°	343875
30°	107443
35°	47761
40°	22155
45°	10466
50°	5757
55°	3183
60°	1480
65°	817
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P279698

CATALOG NUMBER: LDA2B158040D010 EU2B15FL408040 2LBAD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	409.6	25.1
10°-20°	814.5	50.0
20°-30°	333.6	20.5
30°-40°	55.2	3.4
40°-50°	13.1	0.8
50°-60°	3.4	0.2
60°-70°	0.8	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1557.6	95.5
0°-40°	1612.9	98.9
0°-60°	1629.4	99.9
0°-90°	1630.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1630.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4544	
5°	4431	410
15°	3059	814
25°	632	334
35°	79	55
45°	15	13
55°	4	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279698

CATALOG NUMBER: LDA2B158040D010 EU2B15FL408040 2LBAD1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	4543.9
1°	4528.1
2°	4507.2
3°	4488.5
4°	4463.8
5°	4430.8
6°	4382.2
7°	4318.6
8°	4228.0
9°	4118.0
10°	3992.3
11°	3846.3
12°	3681.6
13°	3493.8
14°	3285.0
15°	3058.9
17.5°	2425.7
20°	1761.9
22.5°	1127.9
25°	631.7
27.5°	333.1
30°	188.6
32.5°	119.8
35°	79.3
37.5°	52.4
40°	34.4
42.5°	22.5
45°	15.0
47.5°	10.5
50°	7.5
52.5°	5.2
55°	3.7
57.5°	2.2
60°	1.5
62.5°	0.7
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279698

CATALOG NUMBER: LDA2B158040D010 EU2B15FL408040 2LBAD1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)