

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P496279

Luminaire Tested: **LDA2B109035R65D010 2LBDL1H**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P496279
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-68)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B109035R65D010 2LBDL1H
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 828.0 lumens
Efficiency: N/A
Efficacy: 82.8 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.94
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P496279
CATALOG NUMBER: LDA2B109035R65D010 2LBDL1H

Luminous Intensity Polar Plot





TEST NUMBER: P496279

CATALOG NUMBER: LDA2B109035R65D010 2LBDL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	87
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	78	76	74
5	92	83	77	73	90	82	76	72	80	75	72	79	74	71	77	73	70	69
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60
8	78	68	62	58	77	68	62	58	67	61	58	66	61	57	65	60	57	56
9	74	64	58	54	73	64	58	54	63	58	54	62	57	54	61	57	53	52
10	71	61	55	51	70	60	54	51	59	54	50	59	54	50	58	53	50	49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	433221
5°	415165
10°	395368
15°	375770
20°	349561
25°	322699
30°	280000
35°	200922
40°	109100
45°	46608
50°	20033
55°	7225
60°	1283
65°	1051
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P496279

CATALOG NUMBER: LDA2B109035R65D010 2LBDL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.5	9.5
10°-20°	206.1	24.9
20°-30°	269.4	32.5
30°-40°	205.0	24.8
40°-50°	59.3	7.2
50°-60°	8.9	1.1
60°-70°	0.8	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	554.0	66.9
0°-40°	759.0	91.7
0°-60°	827.1	99.9
0°-90°	828.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	828.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	878	
5°	838	78
15°	736	206
25°	593	269
35°	334	205
45°	67	59
55°	8	9
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P496279

CATALOG NUMBER: LDA2B109035R65D010 2LBDL1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	878.1
1°	875.0
2°	870.2
3°	860.4
4°	849.8
5°	838.3
6°	827.3
7°	817.5
8°	808.2
9°	799.8
10°	789.2
11°	779.9
12°	770.2
13°	760.5
14°	749.8
15°	735.7
16°	725.1
17°	712.2
18°	692.8
19°	682.6
20°	665.8
21°	650.7
22.5°	627.7
23°	618.9
24°	605.2
25°	592.8
26°	576.4
27°	558.3
28°	538.4
29°	517.1
30°	491.5
32.5°	421.1
35°	333.6
37.5°	246.0
40°	169.4
42.5°	107.5
45°	66.8
47.5°	41.6
50°	26.1
52.5°	15.5
55°	8.4
57.5°	3.1
60°	1.3
62.5°	0.9
65°	0.9



TEST NUMBER: P496279

CATALOG NUMBER: LDA2B109035R65D010 2LBDL1H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)