

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278808

Luminaire Tested: **LDA2B158040D010 EU2B15NFL258040 2LBAD1WHH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P278808
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B158040D010 EU2B15NFL258040 2LBAD1WHH
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in ADJ spun Refl, Self-Flanged, WHH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1586.9 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P278808

CATALOG NUMBER: LDA2B158040D010 EU2B15NFL258040 2LBAD1WHH

Luminous Intensity Polar Plot





TEST NUMBER: P278808

CATALOG NUMBER: LDA2B158040D010 EU2B15NFL258040 2LBAD1WHH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																											
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97									97																											
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94									94																											
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91									91																											
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89									89																											
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86									86																											
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84									84																											
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82									82																											
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80									80																											
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78									78																											
10	90	84	80	78	90	84	80	78	83	80	78	82	79	77	82	79	77	76									76																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4061897
5°	3746043
10°	2524401
15°	1244634
20°	531640
25°	208982
30°	82263
35°	36077
40°	17325
45°	8373
50°	4605
55°	2580
60°	1480
65°	817
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P278808

CATALOG NUMBER: LDA2B158040D010 EU2B15NFL258040 2LBAD1WHH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	640.7	40.4
10°-20°	690.1	43.5
20°-30°	199.2	12.6
30°-40°	42.1	2.7
40°-50°	10.4	0.7
50°-60°	3.0	0.2
60°-70°	1.0	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1530.0	96.4
0°-40°	1572.1	99.1
0°-60°	1585.4	99.9
0°-90°	1586.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1586.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8233	
5°	7564	641
15°	2437	690
25°	384	199
35°	60	42
45°	12	10
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278808

CATALOG NUMBER: LDA2B158040D010 EU2B15NFL258040 2LBAD1WHH

CANDELA DISTRIBUTION (FULL):

	0°
0°	8233.1
1°	8181.5
2°	8093.9
3°	7975.7
4°	7808.0
5°	7564.0
6°	7234.8
7°	6805.2
8°	6276.8
9°	5660.9
10°	5039.0
11°	4410.3
12°	3816.8
13°	3290.0
14°	2826.7
15°	2436.8
17.5°	1610.5
20°	1012.6
22.5°	622.7
25°	383.9
27.5°	234.2
30°	144.4
32.5°	91.3
35°	59.9
37.5°	39.7
40°	26.9
42.5°	18.7
45°	12.0
47.5°	7.5
50°	6.0
52.5°	4.5
55°	3.0
57.5°	2.2
60°	1.5
62.5°	1.5
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.0
77.5°	0.7
80°	0.0
82.5°	0.0



TEST NUMBER: P278808

CATALOG NUMBER: LDA2B158040D010 EU2B15NFL258040 2LBAD1WHH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)