

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P496289

Luminaire Tested: **LDA2B109035R65D010 2LBDLC1MW**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P496289  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-68)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B109035R65D010 2LBDLC1MW  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3500K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 895.8 lumens  
Efficiency: N/A  
Efficacy: 89.6 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.94  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P496289

CATALOG NUMBER: LDA2B109035R65D010 2LBDLC1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P496289

CATALOG NUMBER: LDA2B109035R65D010 2LBDLC1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97	96	95	93
2	108	103	99	95	105	101	97	94	98	95	92		95	92	90		92	90	88	87
3	102	96	90	86	100	94	89	86	91	88	84		89	86	83		87	84	82	80
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82	78	76	74
5	92	83	77	73	90	82	76	72	80	75	72		79	74	71		77	73	70	69
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73	69	65	64
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68	64	61	60
8	78	68	62	58	77	68	62	58	67	61	58		66	61	57		65	60	57	56
9	74	64	58	54	73	64	58	54	63	57	54		62	57	54		61	57	53	52
10	71	61	55	51	70	60	54	51	59	54	50		59	54	50		58	53	50	49

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	468644
5°	449089
10°	427680
15°	406467
20°	378123
25°	349101
30°	302902
35°	217304
40°	118052
45°	50445
50°	21644
55°	7827
60°	1381
65°	1167
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P496289

CATALOG NUMBER: LDA2B109035R65D010 2LBDLC1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	84.9	9.5
10°-20°	222.9	24.9
20°-30°	291.5	32.5
30°-40°	221.7	24.8
40°-50°	64.1	7.2
50°-60°	9.6	1.1
60°-70°	0.9	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	599.3	66.9
0°-40°	821.0	91.7
0°-60°	894.7	99.9
0°-90°	895.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	895.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	950	
5°	907	85
15°	796	223
25°	641	291
35°	361	222
45°	72	64
55°	9	10
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P496289

CATALOG NUMBER: LDA2B109035R65D010 2LBDLC1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	949.9
1°	946.6
2°	941.3
3°	930.8
4°	919.3
5°	906.8
6°	894.9
7°	884.4
8°	874.3
9°	865.2
10°	853.7
11°	843.7
12°	833.1
13°	822.6
14°	811.1
15°	795.8
16°	784.3
17°	770.5
18°	749.4
19°	738.4
20°	720.2
21°	703.9
22.5°	679.1
23°	669.5
24°	654.7
25°	641.3
26°	623.5
27°	603.9
28°	582.4
29°	559.4
30°	531.7
32.5°	455.6
35°	360.8
37.5°	266.1
40°	183.3
42.5°	116.3
45°	72.3
47.5°	45.0
50°	28.2
52.5°	16.7
55°	9.1
57.5°	3.3
60°	1.4
62.5°	1.0
65°	1.0



TEST NUMBER: P496289

CATALOG NUMBER: LDA2B109035R65D010 2LBDLC1MW

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)