

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278817

Luminaire Tested: **LDA2B158040D010 EU2B15NFL258040 2LBALD1GPH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P278817  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B158040D010 EU2B15NFL258040 2LBALD1GPH  
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC AND 2in ADJ spun Refl w/lens Self-Flanged, GPH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1480.2 lumens  
Efficiency: N/A  
Efficacy: 105.0 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P278817

CATALOG NUMBER: LDA2B158040D010 EU2B15NFL258040 2LBALD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P278817

CATALOG NUMBER: LDA2B158040D010 EU2B15NFL258040 2LBALD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100													
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97	97	97	97	97	97	97													
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94	94	94	94	94	94	94													
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91	91	91	91	91	91	91													
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89	89	89	89	89	89	89													
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86	86	86	86	86	86	86													
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84	84	84	84	84	84	84													
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82	82	82	82	82	82	82													
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80	80	80	80	80	80	80													
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	78	78	78	78	78	78													
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76	76	76	76	76	76	76													

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3788723
5°	3494161
10°	2354622
15°	1160919
20°	495886
25°	194937
30°	76737
35°	33607
40°	16165
45°	7814
50°	4298
55°	2408
60°	1381
65°	817
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P278817

CATALOG NUMBER: LDA2B158040D010 EU2B15NFL258040 2LBALD1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	597.6	40.4
10°-20°	643.6	43.5
20°-30°	185.8	12.6
30°-40°	39.2	2.6
40°-50°	9.7	0.7
50°-60°	2.8	0.2
60°-70°	0.9	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1427.1	96.4
0°-40°	1466.4	99.1
0°-60°	1478.8	99.9
0°-90°	1480.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1480.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7679	
5°	7055	598
15°	2273	644
25°	358	186
35°	56	39
45°	11	10
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278817

CATALOG NUMBER: LDA2B158040D010 EU2B15NFL258040 2LBALD1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7679.4
1°	7631.3
2°	7549.6
3°	7439.3
4°	7282.9
5°	7055.4
6°	6748.2
7°	6347.5
8°	5854.7
9°	5280.2
10°	4700.1
11°	4113.7
12°	3560.1
13°	3068.7
14°	2636.6
15°	2272.9
17.5°	1502.2
20°	944.5
22.5°	580.8
25°	358.1
27.5°	218.5
30°	134.7
32.5°	85.2
35°	55.8
37.5°	37.0
40°	25.1
42.5°	17.5
45°	11.2
47.5°	7.0
50°	5.6
52.5°	4.2
55°	2.8
57.5°	2.1
60°	1.4
62.5°	1.4
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.0
77.5°	0.7
80°	0.0
82.5°	0.0



TEST NUMBER: P278817

CATALOG NUMBER: LDA2B158040D010 EU2B15NFL258040 2LBALD1GPH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)