

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280601

Luminaire Tested: **LDA2B158040D010 EU2B15WFL558040 2LBAD1GPH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P280601  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B158040D010 EU2B15WFL558040 2LBAD1GPH  
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND  
2in ADJ spun Refl, Self-Flanged, GPH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1607.2 lumens  
Efficiency: N/A  
Efficacy: 114.0 lumens/watt  
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P280601

CATALOG NUMBER: LDA2B158040D010 EU2B15WFL558040 2LBAD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P280601

CATALOG NUMBER: LDA2B158040D010 EU2B15WFL558040 2LBAD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |   |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    | 0  |   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |   |
| 1   | 114 | 112 | 109 | 107 | 112 | 110 | 108 | 106 | 106 | 104 | 103 | 102 | 101 | 99  | 98  | 97  | 97  | 95  |    |    |   |
| 2   | 109 | 105 | 101 | 98  | 107 | 103 | 100 | 97  | 100 | 98  | 95  | 97  | 95  | 93  | 95  | 93  | 91  | 90  |    |    |   |
| 3   | 105 | 99  | 95  | 91  | 103 | 98  | 94  | 91  | 95  | 92  | 89  | 93  | 90  | 88  | 91  | 88  | 86  | 85  |    |    |   |
| 4   | 100 | 94  | 89  | 85  | 99  | 93  | 88  | 85  | 91  | 87  | 84  | 89  | 85  | 83  | 87  | 84  | 82  | 80  |    |    |   |
| 5   | 96  | 89  | 84  | 80  | 95  | 88  | 83  | 80  | 86  | 82  | 79  | 85  | 81  | 78  | 83  | 80  | 78  | 76  |    |    |   |
| 6   | 92  | 84  | 79  | 75  | 91  | 84  | 79  | 75  | 82  | 78  | 75  | 81  | 77  | 74  | 80  | 76  | 74  | 72  |    |    |   |
| 7   | 88  | 80  | 75  | 71  | 87  | 80  | 75  | 71  | 78  | 74  | 71  | 77  | 73  | 70  | 76  | 73  | 70  | 69  |    |    |   |
| 8   | 85  | 76  | 71  | 68  | 84  | 76  | 71  | 67  | 75  | 70  | 67  | 74  | 70  | 67  | 73  | 69  | 67  | 65  |    |    |   |
| 9   | 81  | 73  | 68  | 64  | 80  | 72  | 68  | 64  | 72  | 67  | 64  | 71  | 67  | 64  | 70  | 66  | 64  | 62  |    |    |   |
| 10  | 78  | 70  | 65  | 61  | 77  | 69  | 64  | 61  | 69  | 64  | 61  | 68  | 64  | 61  | 67  | 63  | 61  | 59  |    |    |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1372681 |
| 5°  | 1344693 |
| 10° | 1250478 |
| 15° | 1091813 |
| 20° | 903935  |
| 25° | 691343  |
| 30° | 378328  |
| 35° | 140031  |
| 40° | 48496   |
| 45° | 21839   |
| 50° | 10285   |
| 55° | 5161    |
| 60° | 1480    |
| 65° | 817     |
| 70° | 1010    |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |



TEST NUMBER: P280601

CATALOG NUMBER: LDA2B158040D010 EU2B15WFL558040 2LBAD1GPH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 252.3  | 15.7      |
| 10°-20°   | 590.8  | 36.8      |
| 20°-30°   | 558.4  | 34.7      |
| 30°-40°   | 171.9  | 10.7      |
| 40°-50°   | 27.2   | 1.7       |
| 50°-60°   | 5.7    | 0.4       |
| 60°-70°   | 0.8    | 0.0       |
| 70°-80°   | 0.1    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1401.5 | 87.2      |
| 0°-40°    | 1573.4 | 97.9      |
| 0°-60°    | 1606.3 | 99.9      |
| 0°-90°    | 1607.2 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1607.2 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2782 |      |
| 5°  | 2715 | 252  |
| 15° | 2138 | 591  |
| 25° | 1270 | 558  |
| 35° | 232  | 172  |
| 45° | 31   | 27   |
| 55° | 6    | 6    |
| 65° | 1    | 1    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P280601

CATALOG NUMBER: LDA2B158040D010 EU2B15WFL558040 2LBAD1GPH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 2782.3 |
| 1°    | 2771.8 |
| 2°    | 2759.2 |
| 3°    | 2748.7 |
| 4°    | 2735.3 |
| 5°    | 2715.2 |
| 6°    | 2689.1 |
| 7°    | 2654.1 |
| 8°    | 2607.1 |
| 9°    | 2552.7 |
| 10°   | 2496.1 |
| 11°   | 2433.5 |
| 12°   | 2367.1 |
| 13°   | 2294.8 |
| 14°   | 2219.6 |
| 15°   | 2137.6 |
| 17.5° | 1920.7 |
| 20°   | 1721.7 |
| 22.5° | 1519.7 |
| 25°   | 1270.0 |
| 27.5° | 968.9  |
| 30°   | 664.1  |
| 32.5° | 407.7  |
| 35°   | 232.5  |
| 37.5° | 129.7  |
| 40°   | 75.3   |
| 42.5° | 47.0   |
| 45°   | 31.3   |
| 47.5° | 20.9   |
| 50°   | 13.4   |
| 52.5° | 8.9    |
| 55°   | 6.0    |
| 57.5° | 3.7    |
| 60°   | 1.5    |
| 62.5° | 0.7    |
| 65°   | 0.7    |
| 67.5° | 0.7    |
| 70°   | 0.7    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |



TEST NUMBER: P280601

CATALOG NUMBER: LDA2B158040D010 EU2B15WFL558040 2LBAD1GPH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







|       |  |     |
|-------|--|-----|
| 85°   |  | 0.0 |
| 87.5° |  | 0.0 |



(END OF REPORT)