

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278647

Luminaire Tested: **LDA2B109030D010 EU2B10NFL259030 2LBAD1WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P278647
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B109030D010 EU2B10NFL259030 2LBAD1WH
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in ADJ spun Refl, Self-Flanged, WH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 914.0 lumens
Efficiency: N/A
Efficacy: 91.4 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P278647

CATALOG NUMBER: LDA2B109030D010 EU2B10NFL259030 2LBAD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P278647

CATALOG NUMBER: LDA2B109030D010 EU2B10NFL259030 2LBAD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78
10	90	84	80	78	90	84	80	78	83	80	78	82	79	77	82	79	77	76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2339620
5°	2157689
10°	1454023
15°	716911
20°	306194
25°	120359
30°	47398
35°	20779
40°	9983
45°	4814
50°	2610
55°	1462
60°	888
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P278647

CATALOG NUMBER: LDA2B109030D010 EU2B10NFL259030 2LBAD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	369.1	40.4
10°-20°	397.5	43.5
20°-30°	114.7	12.6
30°-40°	24.2	2.6
40°-50°	6.0	0.7
50°-60°	1.7	0.2
60°-70°	0.6	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	881.3	96.4
0°-40°	905.5	99.1
0°-60°	913.2	99.9
0°-90°	914.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	914.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4742	
5°	4357	369
15°	1404	397
25°	221	115
35°	34	24
45°	7	6
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278647

CATALOG NUMBER: LDA2B109030D010 EU2B10NFL259030 2LBAD1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4742.2
1°	4712.4
2°	4662.0
3°	4593.9
4°	4497.3
5°	4356.8
6°	4167.1
7°	3919.7
8°	3615.4
9°	3260.6
10°	2902.4
11°	2540.3
12°	2198.5
13°	1895.0
14°	1628.1
15°	1403.6
17.5°	927.7
20°	583.2
22.5°	358.6
25°	221.1
27.5°	134.9
30°	83.2
32.5°	52.6
35°	34.5
37.5°	22.8
40°	15.5
42.5°	10.8
45°	6.9
47.5°	4.3
50°	3.4
52.5°	2.6
55°	1.7
57.5°	1.3
60°	0.9
62.5°	0.9
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.4
80°	0.0
82.5°	0.0



TEST NUMBER: P278647

CATALOG NUMBER: LDA2B109030D010 EU2B10NFL259030 2LBAD1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)