

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P497865

Luminaire Tested: **LDA2B158040R20D010 2LBDLC1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P497865  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B158040R20D010 2LBDLC1MMS  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 4000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1517.3 lumens  
Efficiency: N/A  
Efficacy: 107.6 lumens/watt  
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.34  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P497865

CATALOG NUMBER: LDA2B158040R20D010 2LBDLC1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P497865

CATALOG NUMBER: LDA2B158040R20D010 2LBDLC1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105		104	103	102		100	100	99	97
2	112	109	106	104	110	107	105	102	104	102	100		101	100	98		98	97	96	95
3	109	105	101	99	107	103	100	98	101	98	96		99	97	95		97	95	94	92
4	106	101	98	95	104	100	97	94	98	95	93		96	94	92		95	93	91	90
5	103	98	94	92	102	97	94	91	96	93	90		94	92	90		93	91	89	88
6	101	95	91	89	100	95	91	88	93	90	88		92	89	87		91	89	87	86
7	98	93	89	86	97	92	89	86	91	88	86		90	87	85		89	87	85	84
8	96	90	87	84	95	90	86	84	89	86	84		88	85	83		87	85	83	82
9	94	88	85	82	93	88	84	82	87	84	82		86	84	82		86	83	81	81
10	92	86	83	80	91	86	83	80	85	82	80		85	82	80		84	82	80	79

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	5015861
5°	4239556
10°	2583216
15°	1062750
20°	382638
25°	153456
30°	69729
35°	32824
40°	17260
45°	9349
50°	5449
55°	2752
60°	1579
65°	934
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P497865

CATALOG NUMBER: LDA2B158040R20D010 2LBDLC1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	706.1	46.5
10°-20°	610.7	40.3
20°-30°	147.2	9.7
30°-40°	37.7	2.5
40°-50°	11.3	0.7
50°-60°	3.2	0.2
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1464.1	96.5
0°-40°	1501.9	99.0
0°-60°	1516.5	99.9
0°-90°	1517.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1517.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10167	
5°	8560	706
15°	2081	611
25°	282	147
35°	54	38
45°	13	11
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P497865

CATALOG NUMBER: LDA2B158040R20D010 2LBDLC1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	10166.7
1°	10078.2
2°	9867.4
3°	9546.8
4°	9133.8
5°	8560.5
6°	7968.3
7°	7314.5
8°	6635.4
9°	5873.4
10°	5156.4
11°	4407.0
12°	3750.0
13°	3128.6
14°	2558.5
15°	2080.7
16°	1685.9
17°	1361.3
18°	1098.4
19°	903.4
20°	728.8
22.5°	449.3
25°	281.9
27.5°	183.2
30°	122.4
32.5°	80.5
35°	54.5
37.5°	37.9
40°	26.8
42.5°	19.0
45°	13.4
47.5°	10.3
50°	7.1
52.5°	4.7
55°	3.2
57.5°	2.4
60°	1.6
62.5°	0.8
65°	0.8
67.5°	0.8
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0



TEST NUMBER: P497865

CATALOG NUMBER: LDA2B158040R20D010 2LBDLC1MMS

**CANDELA DISTRIBUTION (continued):**

	0°
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)