

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P496436

Luminaire Tested: **LDA2B109040R35D010 2LBPIN1H**

Issue Date: 3/12/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P496436  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-27)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/12/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B109040R35D010 2LBPIN1H  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 4000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 741.4 lumens  
Efficiency: N/A  
Efficacy: 74.1 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.5  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P496436

CATALOG NUMBER: LDA2B109040R35D010 2LBPIN1H

### Luminous Intensity Polar Plot





TEST NUMBER: P496436

CATALOG NUMBER: LDA2B109040R35D010 2LBPIN1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	112	111	109	107	107	105	104		103	102	101		100	99	98	96
2	111	107	104	101	109	105	103	100	102	100	98		100	98	96		97	95	94	93
3	107	102	99	96	105	101	98	95	99	96	93		96	94	92		94	92	91	89
4	104	98	94	91	102	97	93	90	95	92	89		93	90	88		91	89	87	86
5	100	94	90	87	99	93	89	86	92	88	86		90	87	85		89	86	84	83
6	97	91	86	83	96	90	86	83	89	85	82		87	84	82		86	83	81	80
7	94	87	83	80	93	87	83	80	86	82	79		85	81	79		84	81	79	78
8	91	84	80	77	90	84	80	77	83	79	77		82	79	76		81	78	76	75
9	89	82	77	75	88	81	77	74	80	77	74		80	76	74		79	76	74	73
10	86	79	75	72	85	79	75	72	78	74	72		77	74	72		77	74	72	71

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1165123
5°	1120792
10°	1015071
15°	706593
20°	346254
25°	129178
30°	56741
35°	27585
40°	12623
45°	6838
50°	3377
55°	946
60°	395
65°	467
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P496436

CATALOG NUMBER: LDA2B109040R35D010 2LBPIN1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	209.1	28.2
10°-20°	366.5	49.4
20°-30°	124.9	16.8
30°-40°	31.1	4.2
40°-50°	8.0	1.1
50°-60°	1.5	0.2
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	700.5	94.5
0°-40°	731.6	98.7
0°-60°	741.1	100.0
0°-90°	741.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	741.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2362	
5°	2263	209
15°	1383	367
25°	237	125
35°	46	31
45°	10	8
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P496436

CATALOG NUMBER: LDA2B109040R35D010 2LBPIN1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2361.6
1°	2356.9
2°	2338.7
3°	2321.2
4°	2293.3
5°	2263.1
6°	2233.7
7°	2206.1
8°	2146.5
9°	2088.7
10°	2026.2
11°	1923.7
12°	1812.5
13°	1669.3
14°	1536.7
15°	1383.4
16°	1233.7
17°	1077.8
18°	932.1
19°	784.5
20°	659.5
21°	540.3
22.5°	396.4
23°	356.1
24°	290.7
25°	237.3
26°	196.2
27°	163.9
28°	138.1
29°	116.6
30°	99.6
32.5°	67.6
35°	45.8
37.5°	30.9
40°	19.6
42.5°	13.4
45°	9.8
47.5°	6.9
50°	4.4
52.5°	2.5
55°	1.1
57.5°	0.7
60°	0.4
62.5°	0.4
65°	0.4



TEST NUMBER: P496436

CATALOG NUMBER: LDA2B109040R35D010 2LBPIN1H

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)