

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P496504

Luminaire Tested: **LDA2B109040R65D010 2LBDLC1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P496504  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-68)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B109040R65D010 2LBDLC1MMS  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 4000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 914.8 lumens  
Efficiency: N/A  
Efficacy: 91.5 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.94  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P496504

CATALOG NUMBER: LDA2B109040R65D010 2LBDLC1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P496504

CATALOG NUMBER: LDA2B109040R65D010 2LBDLC1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97	96	95	93
2	108	103	99	95	105	101	97	94	98	95	92		95	92	90		92	90	88	87
3	102	96	90	86	100	94	89	86	91	88	84		89	86	83		87	84	82	80
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82	78	76	74
5	92	83	77	73	90	82	76	72	80	75	72		79	74	71		77	73	70	69
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73	69	65	64
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68	64	61	60
8	78	68	62	58	77	68	62	58	67	61	58		66	61	57		65	60	57	56
9	74	64	58	54	73	64	58	54	63	57	54		62	57	54		61	57	53	52
10	71	61	55	51	70	60	54	51	59	54	50		59	54	50		58	53	50	49

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	478610
5°	458648
10°	436798
15°	415099
20°	386156
25°	356504
30°	309339
35°	221941
40°	120564
45°	51492
50°	22105
55°	7999
60°	1480
65°	1167
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P496504

CATALOG NUMBER: LDA2B109040R65D010 2LBDLC1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	86.7	9.5
10°-20°	227.7	24.9
20°-30°	297.7	32.5
30°-40°	226.4	24.8
40°-50°	65.5	7.2
50°-60°	9.8	1.1
60°-70°	0.9	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	612.0	66.9
0°-40°	838.5	91.7
0°-60°	913.8	99.9
0°-90°	914.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	914.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	970	
5°	926	87
15°	813	228
25°	655	298
35°	368	226
45°	74	65
55°	9	10
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P496504

CATALOG NUMBER: LDA2B109040R65D010 2LBDLC1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	970.1
1°	966.7
2°	961.3
3°	950.6
4°	938.8
5°	926.1
6°	913.9
7°	903.2
8°	892.9
9°	883.6
10°	871.9
11°	861.6
12°	850.9
13°	840.1
14°	828.4
15°	812.7
16°	801.0
17°	786.8
18°	765.3
19°	754.1
20°	735.5
21°	718.9
22.5°	693.5
23°	683.7
24°	668.6
25°	654.9
26°	636.8
27°	616.8
28°	594.8
29°	571.3
30°	543.0
32.5°	465.3
35°	368.5
37.5°	271.7
40°	187.2
42.5°	118.8
45°	73.8
47.5°	45.9
50°	28.8
52.5°	17.1
55°	9.3
57.5°	3.4
60°	1.5
62.5°	1.0
65°	1.0



TEST NUMBER: P496504

CATALOG NUMBER: LDA2B109040R65D010 2LBDLC1MMS

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)