

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P315062

Luminaire Tested: **LDA2B15NFL8040D010 PINW1MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P315062
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B15NFL8040D010 PINW1MB
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC AND 2in Adj PinHole, White oculus black finish
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1389.5 lumens
Efficiency: N/A
Efficacy: 98.5 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P315062
CATALOG NUMBER: LDA2B15NFL8040D010 PINW1MB

Luminous Intensity Polar Plot





TEST NUMBER: P315062

CATALOG NUMBER: LDA2B15NFL8040D010 PINW1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97																																				
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94																																				
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91																																				
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89																																				
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86																																				
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84																																				
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82																																				
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80																																				
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78																																				
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3556398
5°	3279868
10°	2210241
15°	1089719
20°	465487
25°	182961
30°	72065
35°	31560
40°	15199
45°	7326
50°	3991
55°	2236
60°	1283
65°	817
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P315062

CATALOG NUMBER: LDA2B15NFL8040D010 PINW1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	561.0	40.4
10°-20°	604.2	43.5
20°-30°	174.5	12.6
30°-40°	36.8	2.6
40°-50°	9.1	0.7
50°-60°	2.6	0.2
60°-70°	0.9	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1339.6	96.4
0°-40°	1376.4	99.1
0°-60°	1388.1	99.9
0°-90°	1389.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1389.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7208	
5°	6623	561
15°	2134	604
25°	336	174
35°	52	37
45°	10	9
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P315062

CATALOG NUMBER: LDA2B15NFL8040D010 PINW1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	7208.5
1°	7163.3
2°	7086.7
3°	6983.1
4°	6836.4
5°	6622.7
6°	6334.4
7°	5958.3
8°	5495.7
9°	4956.4
10°	4411.9
11°	3861.5
12°	3341.8
13°	2880.5
14°	2474.9
15°	2133.5
17.5°	1410.1
20°	886.6
22.5°	545.2
25°	336.1
27.5°	205.1
30°	126.5
32.5°	79.9
35°	52.4
37.5°	34.7
40°	23.6
42.5°	16.4
45°	10.5
47.5°	6.6
50°	5.2
52.5°	3.9
55°	2.6
57.5°	2.0
60°	1.3
62.5°	1.3
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.0
77.5°	0.7
80°	0.0
82.5°	0.0



TEST NUMBER: P315062

CATALOG NUMBER: LDA2B15NFL8040D010 PINW1MB

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)