

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279560

Luminaire Tested: **LDA2B109035D010 EU2B10FL409035 2LBAD1WHH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P279560  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B109035D010 EU2B10FL409035 2LBAD1WHH  
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in  
ADJ spun Refl, Self-Flanged, WHH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 973.9 lumens  
Efficiency: N/A  
Efficacy: 97.4 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P279560

CATALOG NUMBER: LDA2B109035D010 EU2B10FL409035 2LBAD1WHH

### Luminous Intensity Polar Plot





TEST NUMBER: P279560

CATALOG NUMBER: LDA2B109035D010 EU2B10FL409035 2LBAD1WHH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																																				
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																																				
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89																																				
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85																																				
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	84	82																																				
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79																																				
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																																				
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																																				
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72																																				
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	73	70	69																																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1339231
5°	1310917
10°	1194770
15°	933373
20°	552588
25°	205443
30°	64204
35°	28548
40°	13267
45°	6210
50°	3454
55°	1892
60°	888
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P279560

CATALOG NUMBER: LDA2B109035D010 EU2B10FL409035 2LBAD1WHH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	244.7	25.1
10°-20°	486.6	50.0
20°-30°	199.3	20.5
30°-40°	33.0	3.4
40°-50°	7.8	0.8
50°-60°	2.1	0.2
60°-70°	0.5	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	930.5	95.5
0°-40°	963.5	98.9
0°-60°	973.4	99.9
0°-90°	973.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	973.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2714	
5°	2647	245
15°	1827	487
25°	377	199
35°	47	33
45°	9	8
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279560

CATALOG NUMBER: LDA2B109035D010 EU2B10FL409035 2LBAD1WHH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2714.5
1°	2705.1
2°	2692.6
3°	2681.4
4°	2666.6
5°	2647.0
6°	2617.9
7°	2579.9
8°	2525.8
9°	2460.1
10°	2384.9
11°	2297.8
12°	2199.4
13°	2087.2
14°	1962.4
15°	1827.4
17.5°	1449.1
20°	1052.5
22.5°	673.8
25°	377.4
27.5°	199.0
30°	112.7
32.5°	71.5
35°	47.4
37.5°	31.3
40°	20.6
42.5°	13.4
45°	8.9
47.5°	6.3
50°	4.5
52.5°	3.1
55°	2.2
57.5°	1.3
60°	0.9
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279560

CATALOG NUMBER: LDA2B109035D010 EU2B10FL409035 2LBAD1WHH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)