

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P498064

Luminaire Tested: **LDA2B158050R20D010 2LBDC1MMS**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P498064  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B158050R20D010 2LBDC1MMS  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 5000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1507.3 lumens  
Efficiency: N/A  
Efficacy: 106.9 lumens/watt  
Spacing Criteria (0/90/45): 0.33 / 0.33 / 0.32  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P498064

CATALOG NUMBER: LDA2B158050R20D010 2LBDC1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P498064

CATALOG NUMBER: LDA2B158050R20D010 2LBDC1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	116	114	112	110	113	111	110	109	108	106	105	104	103	102	101	100	99	98	97	96
2	112	109	106	104	110	107	105	103	104	102	101	102	100	99	99	98	97	96	95	94
3	109	105	102	100	108	104	101	99	102	99	97	99	97	96	97	96	94	93	92	91
4	107	102	99	96	105	101	98	95	99	96	94	97	95	93	96	94	92	91	90	89
5	104	99	95	93	103	98	95	92	97	94	92	95	93	91	94	92	90	89	88	87
6	102	96	93	90	101	96	92	90	95	92	89	93	91	89	92	90	88	87	86	85
7	100	94	91	88	99	94	90	88	92	90	87	92	89	87	91	88	87	86	85	84
8	98	92	88	86	97	91	88	86	91	88	86	90	87	85	89	87	85	84	83	82
9	96	90	87	84	95	90	86	84	89	86	84	88	86	84	88	85	83	82	81	80
10	94	88	85	83	93	88	85	82	87	84	82	87	84	82	86	84	82	81	80	79

**AVERAGE LUMINANCE (cd/sqm):**

0°	
0°	5586730
5°	4654771
10°	2729850
15°	956153
20°	321840
25°	124006
30°	56969
35°	25236
40°	12301
45°	7187
50°	3914
55°	1290
60°	691
65°	817
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P498064

CATALOG NUMBER: LDA2B158050R20D010 2LBDC1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	769.0	51.0
10°-20°	577.4	38.3
20°-30°	121.3	8.0
30°-40°	29.1	1.9
40°-50°	8.3	0.6
50°-60°	1.8	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1467.7	97.4
0°-40°	1496.8	99.3
0°-60°	1506.9	100.0
0°-90°	1507.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1507.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	11324	
5°	9399	769
15°	1872	577
25°	228	121
35°	42	29
45°	10	8
55°	2	2
65°	1	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P498064

CATALOG NUMBER: LDA2B158050R20D010 2LBDC1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	11323.8
1°	11185.6
2°	10847.5
3°	10458.0
4°	10022.2
5°	9398.9
6°	8737.4
7°	8003.2
8°	7164.6
9°	6317.9
10°	5449.1
11°	4555.4
12°	3768.2
13°	3000.2
14°	2387.9
15°	1872.0
16°	1468.5
17°	1158.3
18°	931.2
19°	754.8
20°	613.0
22.5°	371.9
25°	227.8
27.5°	149.2
30°	100.0
32.5°	61.0
35°	41.9
37.5°	28.7
40°	19.1
42.5°	14.0
45°	10.3
47.5°	7.3
50°	5.1
52.5°	2.9
55°	1.5
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.7
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0



TEST NUMBER: P498064

CATALOG NUMBER: LDA2B158050R20D010 2LBDC1MMS

**CANDELA DISTRIBUTION (continued):**

	0°
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)